

1290780
<https://www.phoenixcontact.com/in/products/1290780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-Temperature transducer, input signals from resistance thermometers in 2, 3, or 4-conductor technology, thermocouples, and mV sources are converted into active 0 mA / 4 mA ... 20 mA non Ex i signals. number of channels: 2, Standard configuration, 5-way isolation, Screw connection

Commercial data

Item number	1290780
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK121W
GTIN	4063151523022
Weight per piece (including packing)	228.6 g
Weight per piece (excluding packing)	228.6 g
Country of origin	DE

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Technical data

Notes

Note on application	Accuracy, typically specified as a percentage of the basic measuring range at U_N , 23°C
Notes on operation	Installation conditions influence the ambient temperature. Please refer to the operating instructions.
Notes on operation	Output behavior = 2.4 mA (0 mA ... 23 mA or "Hold last value" can be configured)
Notes on operation	Sensor set via software or DIP switches
Notes on operation	2-conductor comparison set via DIP switch ADJ
Note on application	The input variables can be set via the ISpac Wizard parameterization software or DIP switches.

Product properties

Product type	Temperature transmitter
Product family	MACX Analog
No. of channels	2
Configuration	Software

Electrical properties

Electrical isolation	5-way isolation
Temperature coefficient, typical	$\leq 0.1\%$ (10 K)
Reverse polarity protection	yes

Electrical isolation Input/output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V _{PP}

Electrical isolation Input/power supply IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V _{PP}

Electrical isolation Input/error message output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V _{PP}

Electrical isolation Input/configuration interface IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V _{PP}

Electrical isolation Output 1/output 2

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

Electrical isolation Output/supply

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Electrical isolation Output/configuration interface

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

Electrical isolation Output/supply/error message output

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

Supply

Nominal supply voltage	24 V DC
Supply voltage range	18 V ... 31.2 V
Power dissipation	≤ 1.9 W
Power consumption	≤ 1.9 W

Input data

Measurement

Description of the input	Resistance thermometer
Sensor types (RTD) that can be used	Pt 100, Pt 250, Pt 500, Pt 1000, Pt 2000, Ni 100, Ni 500, Ni 1000, M50, M53, M100
Temperature measuring range	-200 °C ... 1100 °C (Range depending on the sensor type)
Connection technology	2-, 3-, 4-conductor
Max. permissible overall conductor resistance	50 Ω (per wire, 2-conductor circuit) 100 Ω (per wire, 3-, 4-conductor circuit)
Temperature measuring range	≥ 51 K (Range depending on the sensor type)

Measurement

Description of the input	Thermocouple
Sensor types that can be used (TC)	B, E, J, K, N, R, S, T, L, U, XK
Temperature measuring range	-200 °C ... 1800 °C (Range depending on the sensor type)
Max. permissible overall conductor resistance	≤ 1000 Ω (per wire)
Temperature measuring range	≥ 36 K (Range depending on the sensor type)

Measurement

Description of the input	Potentiometer
Connection technology	3-conductor
Linear resistance measuring range	50 Ω ... 500 Ω 0.5 kΩ ... 5 kΩ 1 kΩ ... 10 kΩ 10 kΩ ... 100 kΩ (with parallel 10 kΩ shunt, no wire-break monitoring)

Output data

Signal: Error message output

Maximum switching voltage	30 V
Max. switching current	100 mA

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Signal: Current

Current output signal	0 mA ... 20 mA (configurable)
	4 mA ... 20 mA (configurable)
	0 mA ... 21 mA (Function area)
Load	0 Ω ... 600 Ω (per channel)

Connection data

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 14

Ex data

Ex installation (EPL)	Gc
Ex i circuits (EPL)	Ga
	Da
	Ma

Safety data

Max. internal inductance L_i	negligible
Max. internal capacitance C_i	negligible
Max. output voltage U_o	6.5 V
Max. output current I_o	19.7 mA
Max. output power P_o	32 mW (linear characteristic curve)
Safety-related maximum voltage U_m	253 V AC
IIA (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	700 mH / 1000 μ F
IIB (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	330 mH / 570 μ F
IIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	90 mH / 25 μ F
I (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	700 mH / 1000 μ F

Interfaces

Designation	Configuration interface
Note	Note on application All device functions and diagnostics
Connection method	4-pos. socket
Type	RS-232-C
Software	ISpac Wizard 9199

Signaling

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer




1290780

<https://www.phoenixcontact.com/in/products/1290780>

Status display	Green LED (supply voltage)
	Red LED (line errors)

Dimensions

Dimensional drawing	
Width	17.5 mm
Height	112.5 mm
Depth	113.7 mm
Depth NS 35/7,5	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)

Material specifications

Flammability rating according to UL 94	V0
Housing material	PA 6.6

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (Terminal blocks)
	IP30 (Housing)
Ambient temperature (operation)	-20 °C ... 70 °C (Stand-alone device: any mounting position)
	-20 °C ... 40 °C (Group assembly: vertical DIN rail without circulating air)
	-20 °C ... 60 °C (Group assembly: vertical DIN rail with circulating air)
	-20 °C ... 50 °C (Group assembly: horizontal DIN rail without circulating air)
	-20 °C ... 70 °C (Group assembly: horizontal DIN rail with circulating air)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

Approvals

ATEX

Identification	Ex II (1) G [Ex ia Ga] IIC
	Ex II (1) D [Ex ia Da] IIIC
	Ex II 3 (1) G Ex nA nC [ia Ga] IIC T4 Gc
	Ex I (M1) [Ex ia Ma] I

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

IECEEx

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex nA nC [ia Ga] IIC T4 Gc
	[Ex ia Ma] I

EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
-------------------------------	---

Standards and regulations

Electrical isolation	5-way isolation
----------------------	-----------------

Mounting

Mounting type	NS 35/15, NS 35/7,5
Mounting position	vertical, horizontal


MACX MCR-EX-AP-2T-2I - Temperature measuring transducer

1290780

<https://www.phoenixcontact.com/in/products/1290780>

Drawings

Block diagram




MACX MCR-EX-AP-2T-2I - Temperature measuring transducer

1290780

<https://www.phoenixcontact.com/in/products/1290780>

Dimensional drawing



MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1290780>



IECEx

Approval ID: IECEx BVS 21.0035X



ATEX

Approval ID: BVS 21 ATEX E 033X

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Classifications

ECLASS

ECLASS-11.0	27210129
ECLASS-12.0	27210129
ECLASS-13.0	27210129

ETIM

ETIM 9.0	EC002919
----------	----------

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead(CAS: 7439-92-1)
SCIP	b0613b0e-2747-427c-8a07-7d54f451fd56

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

Accessories

IFS-USB-PROG-ADAPTER - Programming adapter

2811271

<https://www.phoenixcontact.com/in/products/2811271>



Programming adapter with USB interface, for programming with software. The USB driver is included in the software solutions for the products to be programmed, such as measuring transducers or motor managers.

MACX MCR-PTB - Power and error message module

2865625

<https://www.phoenixcontact.com/in/products/2865625>



Power and fault signaling module with screw connection, including corresponding ME 17,5 TBUS 1,5/ 5-ST-3,81 GY DIN rail connector

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

MACX MCR-PTB-SP - Power and error message module

2924184

<https://www.phoenixcontact.com/in/products/2924184>



Power and fault signaling module with Push-in connection, including corresponding ME 17,5 TBUS 1,5/ 5-ST-3,81 GY DIN rail connector

QUINT4-SYS-PS/1AC/24DC/2.5/SC - Power supply unit

2904614

<https://www.phoenixcontact.com/in/products/2904614>



Primary-switched power supply, QUINT POWER, screw connection, DIN rail mounting, supply of devices possible via the TBUS DIN rail connector, protective coating, input: single-phase, output: 24 V DC/2.5 A

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer




1290780

<https://www.phoenixcontact.com/in/products/1290780>

ME 17,5 TBUS 1,5/ 5-ST-3,81 GY - DIN rail bus connectors

1090049

<https://www.phoenixcontact.com/in/products/1090049>



DIN rail connector, color: gray, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, number of positions: 5, product range: TBUS5-17,5..., pitch: 3.81 mm, mounting: DIN rail mounting, locking: without, mounting method: without, type of packaging: packed in cardboard, Item with gold-plated contacts, bus connectors for connecting with electronics housings, 5 parallel contacts

ME-TBUS-A MC 1,5-2 - DIN rail bus connectors

1351974

<https://www.phoenixcontact.com/in/products/1351974>



DIN rail connector adapter (2-pos.) for connection of MACX MCR-EX-AP ... devices on the right side to the MACX MCR-PTB(-SP) power module with DIN rail connector ME 17,5 TBUS 1,5/5-ST-3,81 GY for bridging the supply voltage.

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

ME-TBUS-A IMC1,5-2 - DIN rail bus connectors

1351982

<https://www.phoenixcontact.com/in/products/1351982>



DIN rail connector adapter (2-pos.) for connection of MACX MCR-EX-AP... devices on the left side to the MACX MCR-PTB(-SP) power module with DIN rail connector ME 17,5 TBUS 1,5/5-ST-3,81 GY for bridging the supply voltage.

MCR-DP - Separating plate

1430594

<https://www.phoenixcontact.com/in/products/1430594>



The partition plate is used to maintain Ex i isolating distances when Ex i and non-Ex i devices are mounted side by side on a DIN rail.

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

MPS-IH WH - Insulating sleeve

0201663

<https://www.phoenixcontact.com/in/products/0201663>

Insulating sleeve, color: white



MPS-IH RD - Insulating sleeve

0201676

<https://www.phoenixcontact.com/in/products/0201676>

Insulating sleeve, color: red



MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780


<https://www.phoenixcontact.com/in/products/1290780>

MPS-IH BU - Insulating sleeve

0201689

<https://www.phoenixcontact.com/in/products/0201689>

Insulating sleeve, color: blue



MPS-IH YE - Insulating sleeve

0201692

<https://www.phoenixcontact.com/in/products/0201692>

Insulating sleeve, color: yellow



MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

MPS-IH GN - Insulating sleeve

0201702

<https://www.phoenixcontact.com/in/products/0201702>

Insulating sleeve, color: green



MPS-IH GY - Insulating sleeve

0201728

<https://www.phoenixcontact.com/in/products/0201728>

Insulating sleeve, color: gray



MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

MPS-IH BK - Insulating sleeve

0201731

<https://www.phoenixcontact.com/in/products/0201731>

Insulating sleeve, color: black



MPS-MT - Test plug

0201744

<https://www.phoenixcontact.com/in/products/0201744>

Test plug, with solder connection up to 1 mm² conductor cross section, number of positions: 1, color: gray



MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

UC-EMLP (11X9) - Plastic label

0819291

<https://www.phoenixcontact.com/in/products/0819291>




Plastic label, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

UC-EMLP (11X9) YE - Plastic label

0822602

<https://www.phoenixcontact.com/in/products/0822602>



Plastic label, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

UC-EMLP (11X9) CUS - Plastic label

0824547

<https://www.phoenixcontact.com/in/products/0824547>




Plastic label, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: adhesive, text field height: 9 mm, text field width: 11 mm

UC-EMLP (11X9) YE CUS - Plastic label

0824548

<https://www.phoenixcontact.com/in/products/0824548>



Plastic label, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: adhesive, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

UC-EMLP (11X9) SR - Plastic label

0828094

<https://www.phoenixcontact.com/in/products/0828094>



Plastic label, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

UC-EMLP (11X9) SR CUS - Plastic label

0828098

<https://www.phoenixcontact.com/in/products/0828098>



Plastic label, can be ordered: by sheet, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 10, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

US-EMLP (11X9) - Plastic label

0828789

<https://www.phoenixcontact.com/in/products/0828789>



Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 135, text field height: 9 mm, text field width: 11 mm

US-EMLP (11X9) YE - Plastic label

0828871

<https://www.phoenixcontact.com/in/products/0828871>



Plastic label, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 135, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

US-EMLP (11X9) SR - Plastic label

0828872

<https://www.phoenixcontact.com/in/products/0828872>




Plastic label, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, Number of individual labels: 135, text field height: 9 mm, text field width: 11 mm

LS-EMLP (11X9) WH - Device marker

0831678

<https://www.phoenixcontact.com/in/products/0831678>



Device marker, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 255, text field height: 9 mm, text field width: 11 mm

MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

LS-EMLP (11X9) SR - Device marker

0831705

<https://www.phoenixcontact.com/in/products/0831705>

Device marker, Sheet, silver, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 255, text field height: 9 mm, text field width: 11 mm




LS-EMLP (11X9) YE - Device marker

0831732

<https://www.phoenixcontact.com/in/products/0831732>

Device marker, Sheet, yellow, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 255, text field height: 9 mm, text field width: 11 mm



MACX MCR-EX-AP-2T-2I - Temperature measuring transducer



1290780

<https://www.phoenixcontact.com/in/products/1290780>

SZS 0,6X3,5 - Screwdriver

1205053

<https://www.phoenixcontact.com/in/products/1205053>



Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in