

# SACC-CI-M12FSL-4FE-L180 THR R - Contact carrier



1420829

<https://www.phoenixcontact.com/in/products/1420829>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 5-position, Socket, straight, M12, coding: L, PCB mounting, THR solder connection

## Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in

## Commercial data

Item number	1420829
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	ABQ
Product key	ABQAGX
GTIN	4055626280547
Weight per piece (including packing)	11.07 g
Weight per piece (excluding packing)	10.732 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Notes on operation	FE not connected to metal parts that can be touched, no protective function

### Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	5
Seal present	yes
Coding	L
Thread type	M12

#### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage $U_N$	63 V
Nominal current $I_N$	16 A

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Interfaces

Signal type/category	Power
----------------------	-------

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 4T

### Connector

#### Connection 1

Head design	Socket
-------------	--------

# SACC-CI-M12FSL-4FE-L180 THR R - Contact carrier



1420829

<https://www.phoenixcontact.com/in/products/1420829>

Head cable outlet	straight
Head thread type	M12
Coding	L

## Cable/line

Signal type/category	Power
----------------------	-------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

### M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111
Note	In line with

## Mounting


Mounting type	PCB mounting
---------------	--------------

## Packaging specifications

Delivery state	with assembly pad
----------------	-------------------

## Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

# SACC-CI-M12FSL-4FE-L180 THR R - Contact carrier




1420829

<https://www.phoenixcontact.com/in/products/1420829>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1420829>

<div> <b>cULus Recognized</b> Approval ID: E468743-20180113</div>				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	63 V	16 A	-	-

# SACC-CI-M12FSL-4FE-L180 THR R - Contact carrier



1420829

<https://www.phoenixcontact.com/in/products/1420829>

## Classifications

### ECLASS

ECLASS-13.0	27440223
-------------	----------

### ETIM

ETIM 9.0	EC003569
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# SACC-CI-M12FSL-4FE-L180 THR R - Contact carrier



1420829

<https://www.phoenixcontact.com/in/products/1420829>

## Accessories

### SACCCIM12FSL4FEL180THRSHSAMPLE - Sample set

1423414

<https://www.phoenixcontact.com/in/products/1423414>



Sample set, Power, 5-position, Socket, straight, coding: L, PCB mounting, THR solder connection

---

### SACC-FP-F-M12/M14 THR PW - Housing screw connection

1420825

<https://www.phoenixcontact.com/in/products/1420825>



Housing screw connection, Socket, M12, Front mounting, THR solder connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239325



# SACC-CI-M12FSL-4FE-L180 THR R - Contact carrier



1420829

<https://www.phoenixcontact.com/in/products/1420829>

## SACC-BP-F-M12/M15-6-THR PW - Housing screw connection

1420827

<https://www.phoenixcontact.com/in/products/1420827>



Housing screw connection, Socket, M12, Rear mounting, THR solder connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239327

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)