
PCIE-1816 PCIE-1816H

500 KS/s, 16-Bit, 16-Ch PCI Express Multifunction DAQ Card 1 MS/s, 16-Bit, 16-Ch PCI Express Multifunction DAQ Card



Features

PCIE-1816

• 16 analog inputs, up to 1 MS/s, 16-bit resolution

PCIE-1816H

• 16 analog inputs, up to 5 MS/s, 16-bit resolution

PCIE-1816/1816H

- 2 analog outputs, up to 3 MS/s, 16-bit resolution
- Supports analog and digital triggers for analog I/O
- Supports waveform generation for analog output
- 24 programmable digital I/O lines
- Two 32-bit programmable counter/timers
- Onboard FIFO memory (8,192 samples)

FCC CE ROHS

Introduction

PCIE-1816/1816H is a 16-ch (up to 5 MS/s) multifunction DAQ card with integrated digital I/O, analog I/O, and counter functions. PCIE-1816/1816H also features analog and digital triggering support, 2-ch 16-bit analog outputs with waveform generation capability, 24-ch programmable digital I/O lines, and two 32-bit general purpose timer/counters.

Specifications

Analog Input

Channels Single end 16Differential 8

• Resolution 16 bits

• Sample Rate PCIE-1816 Single channel 1 MS/s max.

Multiple channels 500 kS/s max.

PCIE-1816H Single channel 5 MS/s max.

Multiple channels 1 MS/s max.

Note: The sampling rate of each channel is influenced by the number of used channels. For example, if 4 channels are used, the sampling rate will be 1M/4 = 250 kS/s per channel.

• Trigger Reference Digital and analog triggers

FIFO Size 8,192 samples
 Overvoltage Protection ±15 V
 Input Impedance 1 GΩ

Sampling Mode
 Input Range
 Software and external clock
 Software programmable

Accuracy (New)					
Range	±10 V	±5 V	±2.5 V	±1.25 V	±0.625 V
Accuracy	±0.01 %	±0.01 %	±0.01 %	±0.02 %	±0.025 %
Range		0 ~ 10 V	0 ~ 5 V	0 ~ 2.5 V	0 ~ 1.25 V
Accuracy		±0.01 %	±0.01 %	±0.01 %	±0.01 %

Analog Output

Channels
Resolution
Output Rate
Output Rate

Output Range Software programmable

Internal Reference	Unipolar	0 ~ 5 V 0 ~ 10 V		
iliterilai Neierelice	Bipolar	-5 V ~ 5 V -10 V ~ 10 V		
External Reference		0 ~ +x V @ -x V (-10 < x < 10)		

Slew Rate
 Driving Capability
 20 V/µs
 20 mA

Operation Mode
 Accuracy
 Static update, waveform generation
 INLE: ± 1 LSB, DNLE: ± 1 LSB

Digital I/O

Channels 24Compatibility 5 V/TTL

Input Voltage
 Logic 0: 0.8 V max.
 Logic 1: 2.0 V min.
 Output Voltage
 Logic 0: 0.4 V max.

Logic 1: 4.0 V min.

Output Capability

Logic 1: 4.0 V min.

Sink: 2 mA @ 0.4 V

Output Capability Sink: 2 mA @ 0.4 V Source: 2 mA @ 4.0 V

Counter

Channels
 Resolution
 Compatibility
 Max. Input Frequency
 Pulse Generation
 Timebase Stability
 2
 10 MHz
 Yes
 Timebase Stability

General

Form Factor PCI Express x1

Triggering 2 x Analog/2 x digital (16 bits) 68-pin SCSI, female 175 x 100 mm (6.9 x 3.9) Power Consumption Max.: 3.3 V @ 350 mA

12 V @ 250 mA

Operating Temperature 0 ~ 60 °C (32 ~ 140 °F)
 Storage Temperature -20 °C to 70 °C (-4 °F to 158 °F)
 Storage Humidity 5 ~ 95% RH non-condensing

Ordering Information

PCIE-1816-B
 PCIE-1816H-B
 1 MS/s, 16-bit multifunction card
 5 MS/s, 16-bit multifunction card

Accessories

PCL-10168H-1E
 PCL-10168H-2E
 PCL-10168-1E
 68-pin SCSI shielded cable with noise rejection, 2 m
 68-pin SCSI shielded cable, 1 m

PCL-10168-2E
 ADAM-3968-AE
 1700030423-01
 68-pin DIN rail SCSI wiring board
 10-pin flat cable for MDSI synchronization, 10 cm

AD\ANTECH

Industrial IoT Gateways