



1224 - Worksite-maintenance 360° swivel vices



Description:

- Vices in spheroid graphite cast iron, tensile strength 700 N/mm² minimum.
- Wide bearing base of the prism guide/mobile jaw: lack of guide flexion, vice operation preserved even under heavy loads.
- Interchangeable parallel jaws. High wear resistance, hardness 48/53 HRc.
- Removable V-shaped jaws for tightening the pipes. Hardness 40/46 HRc.
- Adjustment system by 2 complex gap compensation screws.
- Burnished control bar.



	Length L [mm]	Length L1 [mm]	Length L2 [mm]	Length L3 [mm]	Head Width B [mm]	Height H [mm]	Height H1 [mm]	A Maxi [mm]	Weight [Kg]
1224.100	345.0	104.0	51.0	70.0	63.0	164.0	74.0	125.0	9.7
1224.125	380.0	127.0	53.0	76.0	75.0	178.0	83.0	150.0	12.84
1224.150	460.0	154.0	60.0	91.0	95.0	205.0	94.0	200.0	18.88
1224.175	532.0	178.0	68.0	111.0	118.0	241.0	123.0	235.0	26.36