



Interface plug-in relay, 6 A, 1 CO, with LED, 60 V DC

Local distributor code: 398068877

RSL1PRFU

EAN Code: 3606480077920

Main

Range of product	Harmony Electromechanical Relays	
Series name	RSL series	
Product or component type	Pre-assembled plug-in relay with socket	
Relay type	Slim interface relay	
Contact operation	Standard	
Contacts type and composition	1 C/O	
status LED	With	
[Uc] control circuit voltage	110 V AC/DC	
[Ithe] conventional enclosed thermal current	6 A at -4055 °C	

Complementary

Plastic compression spring	
20500 Ohm network: DC at 23 °C +/- 10 %	
6 kV conforming to IEC	
6 A 1 C/O (AC-1/DC-1) conforming to IEC/UL	
100 mA	
12 V	
250 V conforming to IEC 277 V conforming to cUL	
120 mW	
277 V	
>= 0.05 Uc	
6 A at 250 V AC 0.5 mm mounting distance	
60000 cycles for resistive load, 6 A at 250 V, AC-1	
1500 VA 150 W	
5 ms reset 12 ms	
(11-12-14)OC (A1-A2)CO	
0.17 W, DC	
10000000 cycles	
B10d = 60000	

Operating rate	<= 72000 cycles/hour no-load <= 360 cycles/hour under load	
control type	Without lockable test button	
Compatibility code	RSL	
Reset time	20 ms	
Contact terminal arrangement	Separate	
Connections - terminals	Spring terminals, 1 x 0.21 x 1.5 mm² (AWG 24AWG 16) flexible with cable end Spring terminals, 1 x 0.21 x 1.5 mm² (AWG 24AWG 16) solid without cable end	
Clamping force	1040 N	
Protection category	RT III	
Mounting support	35 mm symmetrical DIN rail	
Operating position	Any position	
Test levels	Level A group mounting	
Device presentation	Complete product	
Sale per indivisible quantity	10	
Contacts material	Silver alloy (AgSnO2)	
Shape of pin	Flat (PCB type)	
Width	6.2 mm	
Height	78.6 mm	
Depth	101 mm	
Net weight	0.029 kg	

Environment

Input voltage	110 V AC/DC (input voltage limit: 88126.5 V)	
Dielectric strength	1000 V AC between contacts 4000 V AC between coil and contact	
IP degree of protection	IP40 conforming to IEC 60529	
Ambient air temperature for operation	-4070 °C	
Standards	IEC 61810-1 UL 508 CSA C22.2 No 14	
Product certifications	CSA GOST UL	
Marking	CE	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	10 gn, amplitude = \pm 1 mm (f = 10150 Hz)10 cycles not operating conforming to IEC 60068-2-6 5 gn, amplitude = \pm 1 mm (f = 10150 Hz)10 cycles in operation conforming to IEC 60068-2-6	
Shock resistance	10 gn (duration = 11 ms) for in operation conforming to IEC 60068-2-27 5 gn (duration = 11 ms) for not operating conforming to IEC 60068-2-27	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	0.700 cm
Package 1 Width	8.000 cm
Package 1 Length	9.700 cm
Package 1 Weight	28.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7.000 cm
Package 2 Width	10.800 cm
Package 2 Length	8.500 cm
Package 2 Weight	302.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.600 kg

Logistical informations

Country of origin C

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	4
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again


○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product datasheet

RSL1PRFU

Dimensions Drawings


Dimensions



RSL1PRFU

Technical Illustration

Dimensions



Product datasheet

RSL1PRFU

Image of product / Alternate images

Alternative

