


DESIGN KIT

WCAP-ASLL Aluminum Electrolytic Capacitors

SMT V-Chip – 2000 h to 5000 h @ 105 °C



TECHNICAL DATA:

C:	10 – 6800 μF
U_R :	6.3 – 16 V_{DC}
I_{ripple} :	85 – 1800 mA
D x L:	4 x 5.5 – 16 x 17 mm

Order Code 865 060

Version 1.0

DESIGN KIT

WCAP-ASLL Aluminum Electrolytic Capacitors

SMT V-Chip – 2000 h to 5000 h @ 105 °C



865 060 140 002 6.3 V ASEB055330M6R3DVCTAB000 C: 33 μ F I _{ripple} : 85 mA D x L: 4 x 5.5 mm	865 060 142 003 6.3 V ASEC055470M6R3DVCTBB000 C: 47 μ F I _{ripple} : 160 mA D x L: 5 x 5.5 mm	865 060 143 005 6.3 V ASED055151M6R3DVCTBB000 C: 150 μ F I _{ripple} : 240 mA D x L: 6.3 x 5.5 mm	865 060 145 006 6.3 V ASED077221M6R3DVCTCB000 C: 220 μ F I _{ripple} : 280 mA D x L: 6.3 x 7.7 mm	865 060 153 007 6.3 V ASEE105331M6R3DVCTEE000 C: 330 μ F I _{ripple} : 450 mA D x L: 8 x 10.5 mm	865 060 153 008 6.3 V ASEE105471M6R3DVCTEE000 C: 470 μ F I _{ripple} : 500 mA D x L: 8 x 10.5 mm	865 060 153 009 6.3 V ASEE105681M6R3DVCTEE000 C: 680 μ F I _{ripple} : 550 mA D x L: 8 x 10.5 mm
865 060 153 010 6.3 V ASEE105102M6R3DVCTEE000 C: 1000 μ F I _{ripple} : 550 mA D x L: 8 x 10.5 mm	865 060 157 011 6.3 V ASEF105152M6R3DVCTEE000 C: 1500 μ F I _{ripple} : 690 mA D x L: 10 x 10.5 mm	865 060 162 012 6.3 V ASEH140332M6R3DVCTGE000 C: 3300 μ F I _{ripple} : 1150 mA D x L: 12.5 x 14 mm	865 060 163 013 6.3 V ASEE170682M6R3DVCTHE000 C: 6800 μ F I _{ripple} : 1800 mA D x L: 16 x 17 mm	865 060 240 001 10 V ASEC055220M010DVCTAB000 C: 22 μ F I _{ripple} : 90 mA D x L: 4 x 5.5 mm	865 060 242 002 10 V ASEC055330M010DVCTBB000 C: 33 μ F I _{ripple} : 160 mA D x L: 5 x 5.5 mm	865 060 243 003 10 V ASED055470M010DVCTBB000 C: 47 μ F I _{ripple} : 230 mA D x L: 6.3 x 5.5 mm
865 060 243 004 10 V ASED055101M010DVCTBB000 C: 100 μ F I _{ripple} : 240 mA D x L: 6.3 x 5.5 mm	865 060 243 005 10 V ASED055151M010DVCTBB000 C: 150 μ F I _{ripple} : 250 mA D x L: 6.3 x 5.5 mm	865 060 245 006 10 V ASED077221M010DVCTCB000 C: 220 μ F I _{ripple} : 300 mA D x L: 6.3 x 7.7 mm	865 060 253 007 10 V ASEE105331M010DVCTEE000 C: 330 μ F I _{ripple} : 500 mA D x L: 8 x 10.5 mm	865 060 253 008 10 V ASEE105471M010DVCTEE000 C: 470 μ F I _{ripple} : 550 mA D x L: 8 x 10.5 mm	865 060 257 009 10 V ASEF105681M010DVCTEE000 C: 680 μ F I _{ripple} : 690 mA D x L: 10 x 10.5 mm	865 060 257 010 10 V ASEF105102M010DVCTEE000 C: 1000 μ F I _{ripple} : 690 mA D x L: 10 x 10.5 mm
865 060 262 011 10 V ASEH140222M010DVCTGE000 C: 2200 μ F I _{ripple} : 1150 mA D x L: 12.5 x 14 mm	865 060 263 012 10 V ASEK170472M010DVCTHE000 C: 4700 μ F I _{ripple} : 1800 mA D x L: 16 x 17 mm	865 060 340 001 16 V ASEC055100M016DVCTAB000 C: 10 μ F I _{ripple} : 90 mA D x L: 4 x 5.5 mm	865 060 342 002 16 V ASEC055220M016DVCTBB000 C: 22 μ F I _{ripple} : 150 mA D x L: 5 x 5.5 mm	865 060 343 003 16 V ASEC055330M016DVCTBB000 C: 33 μ F I _{ripple} : 230 mA D x L: 6.3 x 5.5 mm	865 060 343 004 16 V ASED055470M016DVCTBB000 C: 47 μ F I _{ripple} : 230 mA D x L: 6.3 x 5.5 mm	865 060 343 005 16 V ASED055101M016DVCTBB000 C: 100 μ F I _{ripple} : 255 mA D x L: 6.3 x 5.5 mm
865 060 345 006 16 V ASED077151M016DVCTCB000 C: 150 μ F I _{ripple} : 280 mA D x L: 6.3 x 7.7 mm	865 060 345 007 16 V ASED077221M016DVCTCB000 C: 220 μ F I _{ripple} : 280 mA D x L: 6.3 x 7.7 mm	865 060 353 008 16 V ASEE105331M016DVCTEE000 C: 330 μ F I _{ripple} : 550 mA D x L: 8 x 10.5 mm	865 060 353 009 16 V ASEE105471M016DVCTEE000 C: 470 μ F I _{ripple} : 600 mA D x L: 8 x 10.5 mm	865 060 357 010 16 V ASEE105681M016DVCTEE000 C: 680 μ F I _{ripple} : 750 mA D x L: 10 x 10.5 mm	865 060 362 011 16 V ASEH140152M016DVCTGE000 C: 1500 μ F I _{ripple} : 1150 mA D x L: 12.5 x 14 mm	865 060 363 012 16 V ASEE170332M016DVCTHE000 C: 3300 μ F I _{ripple} : 1800 mA D x L: 16 x 17 mm

TECHNICAL DATA:

Capacitance Tolerance: $\pm 20\%$
 Temperature Range: $-55\text{ }^{\circ}\text{C} / +105\text{ }^{\circ}\text{C}$
 I_{ripple}: Max. Values @ 100 kHz / +105 °C
 Endurance: 2000 h to 5000 h @ +105 °C, max. I_{ripple} applied



DC Voltage Rating

6.3 V
10 V
16 V

EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | LEDs | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | REDCUBE TERMINALS | CAPACITORS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2018

www.we-online.com

All products
ex stock!