


AL5021



IO-Link input/output module

IOL MOD 16xDX A 001 000 IP67



Application	
Special feature	Halogen-free; Gold-plated contacts
Electrical data	
Operating voltage [V]	18...30 DC
Current consumption [mA]	50...1050; (US)
Protection class	III
Inputs / outputs	
Total number of inputs and outputs	16
Number of inputs and outputs	Number of digital inputs: 16; Number of digital outputs: 16
Inputs	
Number of digital inputs	16; (parameterisable)
Input circuit of digital inputs	PNP
Sensor supply of the inputs	US
Power supply [V]	18...30
Outputs	
Number of digital outputs	16; (parameterisable)
Max. current load outputs total [A]	1
Short-circuit protection	yes
Actuator supply outputs	US
Interfaces	
Communication interface	IO-Link
SDCI standard	IEC 61131-9
Transmission type	COM3 (230,4 kBaud)

AL5021



IO-Link input/output module

IOL MOD 16xDX A 001 000 IP67

IO-Link revision	1.1	
SIO mode	no	
Required master port type	A	
Min. process cycle time [ms]	1	
Supported DeviceIDs	Type of operation default	DeviceID 1452
Note	For further information please see the IODD PDF file under "Downloads"	

Operating conditions

Ambient temperature [°C]	-25...60
Storage temperature [°C]	-25...70
Max. relative air humidity [%]	90
Max. height above sea level [m]	2000
Protection	IP 67

Tests / approvals

EMC	EN 61000-6-2	
	EN 61000-6-3	
	IEC 61131-9	
	IEC 61131-2 Type 3	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64	
	DIN EN 60068-2-6	

Mechanical data

Weight [g]	233
Dimensions [mm]	107 x 35.4 x 15.1
Materials	housing: PA orange

Displays / operating elements

Display	operation	2 x LED, green
	fault	1 x LED, red

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - IO-Link

Cable: 2 m, PUR, Halogen-free, black, Ø 4.3 mm; 3 x 0.34 mm² (42 x Ø 0.1 mm)

Connector: 1 x M12, straight; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



X1	
1	L+ (US)
3	L- (US)
4	IO-Link

AL5021




IO-Link input/output module

IOL MOD 16xDX A 001 000 IP67

Electrical connection - inputs / outputs

Cable: 1.5 m, PUR, Halogen-free, black, Ø 6.0 mm; 18 x 0.25 mm² (32 x Ø 0.1 mm)

Connection



- Core colours :
- RD = red
 - BU = blue
 - WH = white
 - GY = grey
 - BN = brown
 - GN = green
 - YE = yellow
 - BK = black
 - OG = orange
 - VT = lilac

X1.0...X1.17

1-16	IO-Link
17	L+ (US)
18	L- (US)