



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Dust Cap**

Number of Positions: **24**

Operating Temperature (Max): **105 °C [ 221 °F ]**

Operating Temperature Range: **-55 – 105 °C [ -67 – 221 °F ]**

### Features

#### Product Type Features

Connector Cover Type	Dust Cap
----------------------	----------

#### Configuration Features

Number of Positions	24
---------------------	----

#### Housing Features

Compatible With Connector Shape	D-Shaped
---------------------------------	----------

#### Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

#### Packaging Features

Packaging Method	Package
Packaging Quantity	1

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JUNE 2025 (250)  
Does not contain REACH SVHC

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




## Also in the Series | CHAMP Docking Connectors





IDC D-Sub Connectors(41)



Panel Mount D-Sub Connectors(5)


## Customers Also Bought



TE Part #5-103957-4  
4X5 MTE RCPT SR LATCH .100CL



TE Part #5-103957-5  
4X6 MTE RCPT SR LATCH .100CL



TE Part #640545-1  
MR SPLIT PIN 26-18 PTPHRZ LP



TE Part #3-1437622-0  
KN1251B1/4=KNOB BLK KNURL L/HA




TE Part #1658622-5  
24 NOVO MIL/CTR 30DP,LEAD FREE



TE Part #1676143-2  
RN 0805 100R 0.1% 10PPM 1KRL




TE Part #1676366-2  
RN 0805 51R1 0.1% 10PPM 1KRL



TE Part #3-2176421-9  
TLRP 2512 2.0W R150 1% 25PPM 4K RL



TE Part #6609032-2  
1VR3=F7195 S0



TE Part #103957-7  
2X8 MTE RCPT SR LATCH .100CL

## Documents

### Product Drawings

[COVER, DUST, RCPT, RED, CHAMP](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_229969-4\\_AA.2d\\_dxf.zip](#)

English

[3D PDF](#)



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_229969-4\\_AA.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_229969-4\\_AA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.