

## FEATURES

- Female RJ45 T-adaptor
- Shielded connector, ideal for use in automation facilities
- 2-way splitter
- Cat5 LAN category configuration
- Complies with standards ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007

## RS PRO, Female Cat5 RJ45 Connector

RS Stock No.: 349-3477



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

Need a handy way to reduce all those cables you need to connect computers to a switch or hub? This RJ45 connector easily splits one connection into two, making it the perfect decluttering and space-saving device for setting up networks, such as local area networks (LAN).

This RJ45 T-adapter is a Cat5 LAN connector and is ideal for ethernet cable applications. Wherever a hardwire network connection is preferred over Wi-Fi in LAN setups, such as in libraries, Cat5 connectors are a reliable standard. As it's shielded, this cable is also suitable for environments where electromagnetic interference is a concern including automation and process control facilities.

### General Specifications

|                                |   |
|--------------------------------|---|
| <b>Ethernet Connector Type</b> | RJ45 Connector  |
| <b>Gender</b>                  | Female  |
| <b>LAN Category</b>            | Cat5  |
| <b>Number of Ports</b>         | 1   |
| <b>Number of Ways</b>          | 2   |
| <b>Connector Type</b>          | RJ45 (Socket)   |
| <b>Shield Type</b>             | Shielded  |
| <b>Orientation</b>             | Straight  |
| <b>Applications</b>            | Wireless outdoor AP, Outdoor LED and display lighting, Marine, Machine automation, Military |

### Approvals

|                                  |   |
|----------------------------------|---|
| <b>Compliance/Certifications</b> | ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007 |
|----------------------------------|---|

