

# Product datasheet

Specifications



circuit breaker ComPacT NSXm B  
(25 kA at 415 VAC), 4P 3d, 25 A  
rating TMD trip unit, EverLink  
connectors

C11B6TM025L

EAN Code: 3606481990075

## Main

Range	ComPacT
Product name	ComPacT NSXm
Device short name	NSXm 63B
Product or component type	Circuit breaker
Device application	Distribution
Poles description	4P
Protected poles description	3D
Neutral position	Left
[In] rated current	25 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	50 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	B 25 kA 415 V AC
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	LI
control type	Toggle
Circuit breaker mounting mode	Fixed

## Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ics] rated service short-circuit breaking capacity	50 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	20000 cycles

<b>Electrical durability</b>	20000 cycles at 440 V In/2 10000 cycles at 440 V In 10000 cycles at 690 V In/2 5000 cycles at 690 V In
<b>Power dissipation per pole</b>	2.8 W
<b>Mounting support</b>	Backplate
<b>Mounting position</b>	Horizontal and vertical Flat on the back
<b>Upside connection</b>	Front
<b>Downside connection</b>	Front
<b>Connection terminals</b>	1 Everlink lug wire size 2.5...95 mm <sup>2</sup> , rigid or stranded aluminium/copper 1 Everlink lug wire size 2.5...70 mm <sup>2</sup> , flexible copper
<b>Connection pitch</b>	35 mm with spreaders 27 mm without spreaders
<b>9 mm pitches</b>	12 module
<b>Trip unit rating</b>	25 A at 40 °C
<b>Long-time pick-up adjustment type Ir (thermal protection)</b>	Adjustable
<b>[Ir] long-time protection pick-up adjustment range</b>	0.7...1 x In
<b>Long-time protection delay adjustment type tr</b>	Fixed
<b>Neutral protection settings</b>	No protection (3D)
<b>Instantaneous protection pick-up adjustment type Ii</b>	Fixed
<b>[Ii] instantaneous protection pick-up adjustment range</b>	600 A
<b>Earth-leakage protection</b>	Without
<b>Number of slots for electrical auxiliaries</b>	1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX
<b>Local signalling</b>	Flag (green) for presence of auxiliary contacts
<b>Width (W)</b>	108 mm
<b>Height (H)</b>	137 mm
<b>Depth (D)</b>	80 mm
<b>Net weight</b>	1.42 kg
<b>Colour</b>	Grey (RAL 7016)

## Environment

<b>Standards</b>	EN/IEC 60947-2
<b>Overvoltage category</b>	III
<b>Electrical shock protection class</b>	Class I on front face
<b>Pollution degree</b>	3 conforming to IEC 60664-1
<b>IP degree of protection</b>	IP40 conforming to IEC 60529
<b>IK degree of protection</b>	IK07 conforming to IEC 62262
<b>Ambient air temperature for operation</b>	-25...70 °C
<b>Ambient air temperature for storage</b>	-50...85 °C
<b>Relative humidity</b>	0...95 %

---

<b>Operating altitude</b>	2000 m without derating 5000 m with derating
---------------------------	---

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
-------------------------------	-----

---

<b>Number of Units in Package 1</b>	1
-------------------------------------	---

---

<b>Package 1 Height</b>	12.000 cm
-------------------------	-----------

---

<b>Package 1 Width</b>	13.000 cm
------------------------	-----------

---

<b>Package 1 Length</b>	22.000 cm
-------------------------	-----------

---

<b>Package 1 Weight</b>	1.600 kg
-------------------------	----------

---

<b>Unit Type of Package 2</b>	S03
-------------------------------	-----

---

<b>Number of Units in Package 2</b>	6
-------------------------------------	---

---

<b>Package 2 Height</b>	30.000 cm
-------------------------	-----------

---

<b>Package 2 Width</b>	30.000 cm
------------------------	-----------

---

<b>Package 2 Length</b>	40.000 cm
-------------------------	-----------

---

<b>Package 2 Weight</b>	10.020 kg
-------------------------	-----------

---

<b>Unit Type of Package 3</b>	P12
-------------------------------	-----

---

<b>Number of Units in Package 3</b>	48
-------------------------------------	----

---

<b>Package 3 Height</b>	45.000 cm
-------------------------	-----------

---

<b>Package 3 Width</b>	80.000 cm
------------------------	-----------

---

<b>Package 3 Length</b>	120.000 cm
-------------------------	------------

---

<b>Package 3 Weight</b>	92.160 kg
-------------------------	-----------

## Logistical informations

---

<b>Country of origin</b>	PL
--------------------------	----

## Contractual warranty

---

<b>Warranty (in months)</b>	18
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	60
----------------------------------	----

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	Yes
--------------------------------------	-----

<a href="#">EU RoHS Directive</a>	Compliant with Exemptions
-----------------------------------	---------------------------

SCIP Number	4b89979a-b2b4-46f7-b291-ed2599c8d205
-------------	--------------------------------------

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

Halogen-free status	Halogen free plastic parts product
---------------------	------------------------------------

PVC free	Yes
----------	-----

Silicone-free	No
---------------	----

## Use Again

### Repack and remanufacture

End of life manual availability	No need of specific recycling operations
---------------------------------	--

Take-back	No
-----------	----

WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------------	---

Offer Marketing Illustration

Product benefits / Features

---

## CompacT NSXm Technical Benefits



- Come in one size and are optimized for small spaces.
- 3 or 4 pole versions
- Rated currents: 16 to 160A
- Thermal-magnetic protections
- Breaking capacities under 240/415 V  
16, 25, 36, 50, 70 kA
- Integrated earth leakage protection via MicroLogic Vigi (earth leakage circuit breaker - ELCB)
- EverLink™ connectors for bare cables

Offer Marketing Illustration

Product benefits / Features

---



## Compact NSXm Range Accessories



Wireless  
indication auxiliary



Long terminal  
shield



Standard  
auxiliary contact



Rotary handles



Inter-phase barrier



Toggle padlocking  
device



MN undervoltage  
release



Standard MX shunt  
release


Offer Marketing Illustration

Product benefits / Features

---

## CompacT NSXm

### Technical Features



Offer Marketing Illustration

Product benefits / Features

---

## Compact NSXm Moulded Case Circuit Breaker



### Efficiency

It features integrated earth leakage protection and standardized accessories – which means you save space, time, and effort.



### Reliability

Optimized in size and featuring innovations tailored to your needs. Roto-active™ breaking technology helps to increase operation lifespan.



### Connectivity

Designed to connect to EcoStruxure Power, an IoT-connected architecture for improving every aspect of your power distribution system.



Technical Illustration

Assembly's dimensions

---

