



 PRODUCT-DETAILS

OS160GD01P

OS160GD01P SWITCH FUSE



General Information

Extended Product Type	OS160GD01P
Product ID	1SCA118678R1001
EAN	6417019502496
Catalog Description	OS160GD01P SWITCH FUSE
Long Description	Switch-disconnector fuse, 160A, 1-pole, DIN,000/00, front operated, handle and shaft included.

ABB EcoSolutions

ABB Site Meeting Group Waste To Landfill Target	UL 2799 Zero Waste To Landfill Validation available
End Of Life Disassembling Instructions	1SCC311047M0201
Environmental Product Declaration - EPD	1SCC311196D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC311013C0201
Instructions and Manuals	1SCC311037M0206
Mechanical Drawings	OS160GD_F_01.igs
Environmental Product Declaration - EPD	1SCC311196D0201

Environmental

Degree of Protection	acc. to IEC 60529 IP20
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	77 mm
Product Net Height	140 mm
Product Net Depth / Length	130 mm
Product Net Weight	0.98 kg 2.16 lb

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	192 mm 7.56 in
Package Level 1 Depth / Length	192 mm 7.56 in
Package Level 1 Height	146 mm 5.75 in
Package Level 1 Gross Weight	1.08 kg 2.38 lb
Package Level 1 EAN	6417019502496

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C}$ 160 A
Conventional Thermal Current (I_{the})	Fully Enclosed 160 A
Degree of Protection	acc. to IEC 60529 IP20
Fuse Size	NH000 NH00
Fuse System	DIN
Handle Type	Pistol handle
Mounting Type	Base mounting
Number of Poles	1P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out, Bottom In - Top Out
Power Loss	at Rated Current 8 W
Rated Conditional Short-Circuit Current (I_{nc})	(500 V) 100 kA (690 V) 80 kA
Rated Current (I_n)	Main Circuit 160 A
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Current AC-21A (I_e)	(500 V) 160 A (690 V) 160 A
Rated Operational Current AC-22A (I_e)	(500 V) 160 A (690 V) 160 A
Rated Operational Current AC-23A (I_e)	(500 V) 160 A (690 V) 160 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 45 kW (400 V) 75 kW (415 V) 75 kW (500 V) 90 kW (690 V) 132 kW
Rated Operational Voltage	Main Circuit 690 V AC
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 5 kiloampere rms
Standards	IEC 60947-3
Switches Operating Mechanism	01 (Left Side)
Terminal Type	Lug terminals
Terminal Width	20 mm
Tightening Torque	15 ... 22 N·m

Technical UL/CSA

Tightening Torque	15 ... 22 N·m
-------------------	---------------

Certificates and Declarations

A2L Certificate – IEC	1SCC311209D0201
ATEX Certificate	No certification needed

CCC Certificate	CCC OS100-160G_2015.pdf
Declaration of Conformity - CE	1SCC311137D2703
DNV GL Certificate	1SCC311125D0203
UL Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC001040 - Fuse switch disconnecter
ETIM 10	EC001040 - Fuse switch disconnecter
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5291 >> Fuse switch disconnecter
eClass	V11.1 : 27371401
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Fuses

