

Silicon Carbide (SiC) **Schottky Diode** - EliteSiC, 10 A, 650 V, D1, TO-220F-2L FFSPF1065A

Description


Silicon Carbide (SiC) Schottky Diodes use a completely new technology that provides superior switching performance and higher reliability compared to Silicon. No reverse recovery current, temperature independent switching characteristics, and excellent thermal performance sets Silicon Carbide as the next generation of power semiconductor. System benefits include highest efficiency, faster operating frequency, increased power density, reduced EMI, and reduced system size and cost.

Features

- Max Junction Temperature 175°C
- Avalanche Rated 64 mJ
- High Surge Current Capacity
- Positive Temperature Coefficient
- Ease of Paralleling
- No Reverse Recovery / No Forward Recovery
- This Device is Pb-Free and is RoHS Compliant

Applications

- General Purpose
- SMPS, Solar Inverter, UPS
- Power Switching Circuits




Schottky Diode



TO-220 FP / TO-220F-2FS CASE 221AS

MARKING DIAGRAM



= Assembly Plant Code XYY = Date Code (Year & Week) = Lot Traceability Code FFSPF1065A = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, Unless otherwise specified)

Symbol	Parameter		FFSPF1065A	Unit	
V_{RRM}	Peak Repetitive Reverse Voltage		650	V	
E _{AS}	Single Pulse Avalanche Energy (Note 1)		64	mJ	
lF	Continuous Rectified Forward Current	ard Current @Tc < 110°C		Α	
		@ Tc < 135°C	7.2		
I _{F, Max}	Non-Repetitive Peak Forward Surge Current	Tc = 25°C, 10 μs	720	Α	
		Tc = 150°C, 10 μs	680	Α	
I _{F, SM}	Non-Repetitive Forward Surge Current Half-Sine Pulse, t _P = 8.3 ms		56	Α	
I _{F, RM}	Repetitive Forward Surge Current	Half-Sine Pulse, t _P = 8.3 ms	28	Α	
P _{tot}	Power Dissipation	Tc = 25°C	38	W	
		Tc = 150°C	6.4	W	
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to +175	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected. 1. E_{AS} of 64 mJ is based on starting $T_J = 25^{\circ}C$, L = 0.5 mH, $I_{AS} = 16$ A, V = 50 V.

THERMAL CHARACTERISTICS

Symbol	Parameter	Ratings	Unit
$R_{ heta JC}$	Thermal Resistance, Junction to Case, Max.	3.9	°C/W

PACKAGE MARKING AND ORDERING INFORMATION

Ī	Part Number	Top Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
	FFSPF1065A	FFSPF1065A	TO-220 FP / TO-220F-2FS	Tube	N/A	N/A	50 Units

$\textbf{ELECTRICAL CHARACTERISTICS} \ (T_C = 25^{\circ}C \ unless \ otherwise \ noted)$

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
V _F	Forward Voltage	IF = 10 A, Tc = 25°C	_	1.50	1.75	V
		IF = 10 A, Tc = 125°C	-	1.60	2.0	
		IF = 10 A, Tc = 175°C	-	1.72	2.4	
I _R	Reverse Current	VR = 650 V, Tc = 25°C	-	-	200	μΑ
		VR = 650 V, Tc = 125°C	-	-	400	
		VR = 650 V, Tc = 175°C	-	-	600	
Q_C	Total Capacitance Charge	V = 400 V	-	34	-	nC
С	Total Capacitance	VR = 1 V, f = 100 kHz	-	575	-	pF
		V _R = 200 V, f = 100 kHz	-	62	-	
		VR = 400 V, f = 100 kHz	_	47	-	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS

(T_J = 25°C UNLESS OTHERWISE NOTED)




Figure 1. Forward Characteristics




Figure 3. Current Derating




Figure 5. Capacitive Charge vs. Reverse Voltage




Figure 2. Reverse Characteristics




Figure 4. Power Derating





Figure 6. Capacitance vs. Reverse Voltage

TYPICAL CHARACTERISTICS (CONTINUED)

(T_J = 25°C UNLESS OTHERWISE NOTED)



V_R, Reverse Voltage (V)

Figure 7. Capacitance Stored Energy





Figure 8. Junction-to-Case Transient Thermal Response Curve

TEST CIRCUIT AND WAVEFORMS

$$\label{eq:local_local_local} \begin{split} L &= 0.5 \text{ mH} \\ R &< 0.1 \ \Omega \\ V_{DD} &= 50 \ V \\ EAVL &= 1/2 Li2 \left[V_{R(AVL)} / (V_{R(AVL)} - V_{DD}) \right] \\ Q1 &= IGBT \left(BV_{CES} > DUT \ V_{R(AVL)} \right) \end{split}$$








Figure 9. Unclamped Inductive Switching Test Circuit & Waveform



TO-220 Fullpack, 2-Lead / TO-220F-2FS CASE 221AS ISSUE O

DATE 29 FEB 2012





ON Semiconductor and a retrademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative