



circular conduc. terminal TA4.3 4 x 120...240 mm² for 4 cables; 3 units accessory for: 3VA15; 3VA25

Model		
product brand name	SETRON	
product designation	circular conductor terminal	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA4.3	
type of electrical connection / with control wire tap	No	
Connections according IEC		
connectable conductor cross-section		
• for copper cable / stranded / minimum	120 mm²	
• for copper cable / stranded / maximum	240 mm²	
stripped length	23.1 / 44.5 mm	
tightening torque / when using copper cables		
• stranded	120 - 240 mm²: 36.7 Nm	
• finely stranded	185 mm²: 36.7 Nm	
Connetctions according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C	
stripped length	0.91 / 1.75 in	
connectable conductor cross-section		
• for copper cable / stranded / minimum	4/0 AWG	
• for copper cable / stranded / maximum	500 kcmil	
• for aluminum cable / stranded / minimum	4/0 AWG	
• for aluminum cable / stranded / maximum	500 kcmil	
Certificates		
General Product Approval	EMV	Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

Maritime application other

Environment



[Confirmation](#)

[Miscellaneous](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

[Environmental Confirmations](#)

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9603-0JJ43>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9603-0JJ43>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9603-0JJ43

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/3/2025

