



Image may differ from product. See technical specification for details.

## 23056 CCK/C3W33

**Spherical roller bearing with tapered bore and relubrication features**

Spherical roller bearings can accommodate heavy loads in both directions. They are self-aligning and accommodate misalignment and shaft deflections, with virtually no increase in friction or temperature. The design includes features to facilitate relubrication. The bearings can be used in a modular system, including housings, sleeves and nuts.

- Accommodate misalignment
- High load carrying capacity
- Relubrication features
- Low friction and long service life
- Increased wear resistance

Overview

Dimensions

|                  |        |
|------------------|--------|
| Bore diameter    | 280 mm |
| Outside diameter | 420 mm |
| Width            | 106 mm |

Performance

|                           |              |
|---------------------------|--------------|
| Basic dynamic load rating | 1 797 kN     |
| Basic static load rating  | 2 850 kN     |
| Reference speed           | 1 300 r/min  |
| Limiting speed            | 1 600 r/min  |
| SKF performance class     | SKF Explorer |

Properties

|                                      |              |
|--------------------------------------|--------------|
| Number of rows                       | 2            |
| Locating feature, bearing outer ring | Without      |
| Bore type                            | Tapered 1:12 |
| Cage                                 | Sheet metal  |
| Radial internal clearance            | C3           |
| Tolerance class for dimensions       | Normal       |
| Tolerance class for run-out          | P5           |
| Sealing                              | Without      |
| Lubricant                            | None         |
| Relubrication feature                | With         |
| Candidate for remanufacturing        | Yes          |

Logistics

|                    |             |
|--------------------|-------------|
| Product net weight | 48.5 kg     |
| eClass code        | 23-05-09-11 |
| UNSPSC code        | 31171510    |

Compatible products

Recommended product

|                                                                                                   |                             |
|---------------------------------------------------------------------------------------------------|-----------------------------|
| Withdrawal sleeve, for oil injection, ISO standards                                               | <a href="#">AOH 3056</a>    |
| Adapter sleeve for oil injection mounting with HM lock nut and MS locking clip, metric dimensions | <a href="#">OH 3056 H</a>   |
| Adapter sleeve for oil injection mounting with HM lock nut and MS locking clip, metric dimensions | <a href="#">OH 3156 HTL</a> |



# Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

## Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

## Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

## Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

## Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

## Changes

SKF reserves the right to make changes or additions to this website / app at any time.