

Brush Cutter XGT®, UR016G

40Vmax, 330 mm, 600 W

Model UR016G is cordless Brush Cutter powered by 40Vmax XGT® Li-Ion battery

This model is a cordless solutions for 23mL class entry-level engine grass trimmers. The main features and benefits are: Lightweight design, Good tool weight balance.



XGT **BL** **ADT** **AFT**
MOTOR

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3500 / 5300 / 6500 min ⁻¹
Cutting width	230 / 255 / 330 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	U
Sound Power Level (L _{WA})	94,1 dB(A)
Sound Pressure Level (L _{pA})	82,2 dB(A)
Noise Uncertainty (K Factor)	1,5 - 3 dB(A)
Product net weight	4,0 kg
Tool weight with battery	4,7 - 5,3 kg
Product Dimensions (L x W x H):	1792 x 625 x 537 mm
Nylon line- Diameter	2,0 mm

User benefits

- Reverse switch for easy removal of grass clippings from the cutting tool
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing