



Foot protection

SANTANA S3 SRC

CONSTRUCTION

Non-magnetic high-cut shoe with a wider fit and robust construction for the construction industry



Specific benefits



Comfort

- Wide shape to accommodate stronger foot morphologies
- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Padded collar for comfort and ankle support



Performance

- Metal-free: get through every security gate without a hitch thanks to the absence of metal.
- High stability ensured by the sole's grip properties

Certifications and norms



EN ISO 20345

S3S WPA FO A E CR SR

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Light industry
- Maintenance

Protects against risks



Antistatic



Shock



Slip



Perforation



Foot protection

SANTANA S3 SRC

CONSTRUCTION

Non-magnetic high-cut shoe with a wider fit and robust construction for the construction industry

Standards - Details

Technical details

Shoe type	High shoe
Outsole material	PU, 2d
Anti-perforation insert	Metal free
Upper material	Buffalo leather
Upper finition material	Smooth, Water repellent
Safety toe-cap	Composite
Lining material	Textile, Polyester
Footbed material	EVA, Polyamide
Footbed characteristic	Removable, Breathable, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	720
Size range	39 → 48



Safety footwear

SANTANA S3 SRC

CONSTRUCTION

Non-magnetic high-cut shoe with a wider fit and robust construction for the construction industry

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SANTAS3NO39	Black	39	SANTANA S3 SRC	3295249203160	13295249203167	5	1	8.6 kg	61.0 cm	23.0 cm	34.0 cm
SANTAS3NO40	Black	40	SANTANA S3 SRC	3295249203177	13295249203174	5	1	8.8 kg	61.0 cm	23.0 cm	34.0 cm
SANTAS3NO41	Black	41	SANTANA S3 SRC	3295249203184	13295249203181	5	1	8.9 kg	61.0 cm	23.0 cm	34.0 cm
SANTAS3NO42	Black	42	SANTANA S3 SRC	3295249203191	13295249203198	5	1	9.3 kg	61.0 cm	23.0 cm	34.0 cm
SANTAS3NO43	Black	43	SANTANA S3 SRC	3295249203207	13295249203204	5	1	10.0 kg	25.8 cm	64.6 cm	35.8 cm
SANTAS3NO44	Black	44	SANTANA S3 SRC	3295249203214	13295249203211	5	1	10.1 kg	25.4 cm	65.4 cm	35.6 cm
SANTAS3NO45	Black	45	SANTANA S3 SRC	3295249203221	13295249203228	5	1	10.3 kg	24.8 cm	65.2 cm	36.0 cm
SANTAS3NO46	Black	46	SANTANA S3 SRC	3295249203238	13295249203235	5	1	11.5 kg	31.8 cm	65.8 cm	36.4 cm
SANTAS3NO47	Black	47	SANTANA S3 SRC	3295249203245	13295249203242	5	1	12.4 kg	35.0 cm	72.4 cm	38.4 cm
SANTAS3NO48	Black	48	SANTANA S3 SRC	3295249203252	13295249203259	5	1	12.0 kg	68.2 cm	25.0 cm	36.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height