

# XT1C 160 TMD 160-1600 4p F F InN=100%



XT1C 160 TMD 160-1600 4p F F InN=100%

## General Information

Extended Product Type	XT1C 160 TMD 160-1600 4p F F InN=100%
Product ID	1SDA067410R1
EAN	8015644013042
Catalog Description	XT1C 160 TMD 160-1600 4p F F InN=100%
Long Description	C.BREAKER TMAX XT1C 160 FIXED FOUR-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMD R 160-1600 A FULLY RATED NEUTRAL

## Ordering

EAN	8015644013042
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

## Dimensions

Product Net Width	101.6 mm
Product Net Height	130 mm
Product Net Depth / Length	70 mm
Product Net Weight	1,381 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	128 mm
Package Level 1 Height	135 mm
Package Level 1 Depth / Length	143 mm
Package Level 1 Gross Weight	1,454 kg
Package Level 1 EAN	8015644013042

## Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	Nr. Operations 240 cycles per hour

Nr. Operations 25000 cycle	
Number of Poles	4
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 15 W
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current ( $I_n$ )	160 A
Rated Frequency (f)	50 / 60 Hz
Rated Voltage ( $U_r$ )	690 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Rated Instantaneous Short-Circuit Current Setting ( $I_i$ )	1600 A
Rated Insulation Voltage ( $U_i$ )	800 V
Rated Operational Voltage	690 V AC 500 V DC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(220 V AC) 40 kA (230 V AC) 40 kA (240 V AC) 40 kA (380 V AC) 25 kA (415 V AC) 25 kA (440 V AC) 12.5 kA (500 V AC) 9 kA (525 V AC) 8 kA (690 V AC) 4 kA (250 V DC) 2 Poles in Series 25 kA (500 V DC) 3 Poles in Series 25 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(220 V AC) 40 kA (230 V AC) 40 kA (240 V AC) 40 kA (380 V AC) 25 kA (415 V AC) 25 kA (440 V AC) 25 kA (500 V AC) 18 kA (525 V AC) 8 kA (690 V AC) 4 kA (250 V DC) 2 Poles in Series 25 kA (500 V DC) 3 Poles in Series 25 kA
Rated Uninterrupted Current ( $I_u$ )	160 A
Release Type	TM
Setting Range	112...160 A
Standards	IEC
Sub-type	XT1
Terminal Connection Type	Fixed Circuit-Breakers Front
Version	F

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210033D0204
Declaration of Conformity - CE	9AKK106713A5532
Environmental Information	1SDL000190R0001
GL Certificate	1SDL000163R0103
Instructions and Manuals	1SDH000719R0001
LR Certificate	1SDL000163R0100

---

## Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

