


**52601-G10-8LF - Quickie® : Double Row,  
10 Positions, 2.54 mm (0.1 in.), SMT Header  
0.76 µm (30 µin.) Gold Mating Plating**



[www.fci.com](http://www.fci.com)

## Specifications

### Approvals / Certifications

<b>UL File Number</b>	E66906
<b>CSA File Number</b>	LR46923
<b>Approvals / Certifications</b>	UL and CSA Approved

### Electrical

<b>Current rating</b>	3 amp Continuous
<b>Resistance (Insulation)</b>	10000 M-ohms min.
<b>Voltage rating</b>	500V AC rms min.

### General

<b>Number of contacts (Total)</b>	10
<b>Number of rows</b>	2
<b>Orientation</b>	SMT
<b>Attachment type (Board)</b>	Through Mount
<b>Mating half</b>	All Quickie® Receptacles. Select Discrete Wiring Mini-Latch Housings.

### Mounting

<b>Solder process</b>	Wave Vapor-Phase IR Reflow
-----------------------	----------------------------------

### Other Features

<b>Packaging (Type)</b>	Trays
<b>Type</b>	Low Profile

### Physical

<b>Color (Housing)</b>	Black
<b>Material (Contact)</b>	Copper Alloy
<b>Material (Housing)</b>	High Temperature Thermoplastic
<b>Plating (Contact area)</b>	0.76 µm (30 µin.) Gold
<b>Plating (Tail)</b>	2.54 µm (100 µin.) Pure Tin
<b>Underplating (Contact)</b>	1.27 µm (50 µin.) Nickel
<b>Flammability rating</b>	UL 94V-0
<b>Temperature (Range)</b>	-65°C to +125°C