

CITY M Air Purifier



Advantages

- Healthier employees
- Less cleaning
- Less asthma and allergy suffering
- Reduced environmental impact
- Less odour

Applications: Air purifier for all types of indoor environments, for example hospitals, hotels, offices, homes, schools, public environments and where high quality air purification is required.

Power supply: 200 .. 240 V

Filter: H13/Molecular

Installation: Floor

Design: Multiple colour

Average Air purification area: 75m²

Item no.	Type	Dimensions(WxHxDmm/Weight Kg)	Transport Dimensions(WxHxDmm/Weight Kg)	Filter included in standard version*
94000047	CamCleaner CITY M (WHITE)	329x703x338/15	395X790X395/17	H13/Molecular
94000048	CamCleaner CITY M (BLACK)	329x703x338/15	395X790X395/17	H13/Molecular

Operating specifications

Setting	Air flow m ³ /h	Energy consumption/W	Noise level dBA	System efficiency 0,3-0,4µm (%)
1	37	4	16	>99
2	67	5	16	>99
3	94	6	16	>99
4	127	7	22	>99
5	251	19	38	>99
6	433	55	53	>99