

LED rechargeable hand lamp HL 201 A 250+70 lm, bendable

Handy, compact and reliable.



Product number 1175430020
EAN 4007123691234

DESCRIPTION

- 4 super-bright SMD LEDs with up to 3 hours of light duration.
- Additional switching stage for 1 SMD LED in the light head.
- Bendable mounting base up to +/- 90° with integrated magnet.
- 360° rotatable, retractable hook.
- On/off push button.
- Li-Ion battery 3.7 V/1000mAh with charge indicator.
- USB C charging cable included.

TECHNICAL DATA

Luminous flux	250 lm	Number of batteries	1
Total luminous flux secondary source	70 lm	Battery type	Built-in battery pack
Colour temperature	5700 K	Battery technology	Lithium-ion
Battery capacity	1 Ah	Impact strength	IK07
Battery voltage	3.7 V	Protection class	III
Light duration max.	6 h	Degree of protection (IP)	IP20
Battery charging time approx.	2 h	Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.26 kg
Weight of product (without packaging)	0.13 kg	Dimension LxWxH (incl. packing)	8.7 cm x 6.2 cm x 27.8 cm
Dimension LxWxH (without packing)	3 cm x 4.7 cm x 18.6 cm		

SCOPE OF DELIVERY

LED rechargeable hand lamp HL 201 A, 60cm USB C charging cable