


# NS6 SERIES CONNECTOR

**NS6 Series couplings** couplings feature non-spill valves at a great price. Use the NS6 when even a few drops of spillage pose problems regarding safety, media cost or environmental regulations. These innovative couplings are lightweight, chemically resistant and easy to use. The non-spill design virtually eliminates spills and minimizes downtime. Soft touch overmold makes them comfortable in the hand and very attractive.



## SPECIFICATIONS

### PRESSURE:

Vacuum to 120 psi, 8.3 bar

### TEMPERATURE:

32°F to 160°F (0°C to 71°C)

### MATERIALS:

#### Main components and valves:

Glass-filled polypropylene with TPV\* soft touch overmold

**Thumb latch:** Glass-filled polypropylene

**Valve spring (wetted):** 316 stainless steel

**External spring:** 316 stainless steel

**O-rings:** EPDM

### COLOR:

Gray with dark gray overmold standard; gray with red or blue overmold available†

### TUBING SIZES:

3/8" and 1/2" ID, 9.5 mm and 12.7 mm ID

**LUBRICANTS:** Krytox® PFPE (inert)

### SPILLAGE:

~0.03 cc per disconnect @ 0 psi,

~0.30 cc/disconnect @ 120 psi

**INCLUSION:** 0.42 cc per connect



\*The overmold material is a TPV (thermoplastic vulcanizate). This TPV is an alloy of polypropylene thermoplastic and fully vulcanized EPDM rubber. The material is typically resistant to water, acids and bases.

†NOTE: Standard product is gray, color options require a set-up charge and minimum quantities. Please contact CPC for details.

## FEATURES

- Non-spill design → Disconnect under pressure with no spills
- Color coding → Instant visual differentiation of media lines
- Glass-filled polypropylene → Durable and compatible with many chemicals
- CPC thumb latch → One-hand connection and disconnection

## BENEFITS



These graphs are intended to give you a general idea of the performance capabilities of each product line. The shaded area of each graph represents the operating range of the product family, i.e., upper and lower values are shown. Therefore, depending on the exact coupling configurations selected, you can reasonably expect values to fall within the shaded area.



SCAN

cpcworldwide.com/NS6



### COLDER PRODUCTS COMPANY®

U.S.A.

PHONE: +1 (651) 645-0091

TOLL FREE: +1 (800) 444-2474

E-MAIL: info@cpcworldwide.com

### COLDER PRODUCTS COMPANY GMBH

Germany

E-MAIL: cpcgmbh@cpcworldwide.com

### DOVER (SHANGHAI) INDUSTRIAL CO., LTD

ShangHai, China

PHONE: +86 21 2411 2666

TOLL FREE: +86 400 990 1978

E-MAIL: asiapacific@cpcworldwide.com

# NS6 SERIES DIMENSIONS

## COUPLING BODIES - Polypropylene



TERMINATION	TUBING/THREAD SIZE	METRIC EQ.	SHUTOFF	A	B
IN-LINE PIPE THREAD	1/2" NPT		NS6D10008	1.31 (33.3)	3.01 (76.5)
	1/2" BSPT		NS6D10008BSPT	1.31 (33.3)	3.01 (76.5)
IN-LINE COMPRESSION	1/2" OD	12.7 mm OD	NS6D13008	1.31 (33.3)	3.53 (89.7)
IN-LINE HOSE BARB	3/8" ID	9.5 mm ID	NS6D17006	1.31 (33.3)	3.16 (80.3)
	1/2" ID	12.7 mm ID	NS6D17008	1.31 (33.3)	3.16 (80.3)

## COUPLING INSERTS - Polypropylene




TERMINATION	TUBING/THREAD SIZE	METRIC EQ.	SHUTOFF	A	B
IN-LINE PIPE THREAD	1/2" NPT		NS6D24008	1.31 (33.3)	2.44 (62.0)
	1/2" BSPT		NS6D24008BSPT	1.31 (33.3)	2.44 (62.0)
IN-LINE COMPRESSION	1/2" OD	12.7 mm OD	NS6D20008	1.31 (33.3)	3.01 (76.5)
IN-LINE HOSE BARB	3/8" ID	9.5 mm ID	NS6D22006	1.31 (33.3)	2.59 (65.8)
	1/2" ID	12.7 mm ID	NS6D22008	1.31 (33.3)	2.59 (65.8)
PANEL MOUNT COMPRESSION	1/2" OD	12.7 mm OD	NS6D40008	1.50 (38.1)	3.32 (84.3)
PANEL MOUNT HOSE BARB	3/8" ID	9.5 mm ID	NS6D42006	1.50 (38.1)	2.85 (72.4)
	1/2" ID	12.7 mm ID	NS6D42008	1.50 (38.1)	2.85 (72.4)

All measurements are in inches (millimeters) unless otherwise noted. Tubing must meet stated inside and outside diameters. Couplings are pictured with valves unless otherwise noted.

## ACCESSORIES


DESCRIPTION	MATERIAL	PART NO.
PANEL MOUNT GASKET REPLACEMENT: FOR SEALING PANEL MOUNT BODIES LISTED ABOVE	EPDM	1884300
	FKM	1889600

## PRODUCT DIMENSIONS



## PANEL DIMENSIONS

	PANEL OPENING	PANEL THICKNESS MAX.-MIN.
COUPLING INSERTS	see drawing	0.25 - 0.03



WARRANTY: All sales are subject to the Colder products company® limited express warranty set forth in the CPC catalog. Contact your local distributor or CPC Customer Service for warranty provisions.

Warning: Due to the wide variety of possible fluid media and operating conditions, unintended consequences may result from the use of this product, all of which are beyond the control of CPC. It is the user's responsibility to carefully determine and test for compatibility for use with their application. All such risks shall be assumed by the buyer.

COPYRIGHT © 2026 BY COLDER PRODUCTS COMPANY.

CPC, Colder Products Company, and Colder Products are registered trademarks with the United States Patent and Trademark Office.

For detailed trademark information, please visit: <https://www.cpcworldwide.com/Trademarks>