

DIMENSIONS (in.)								
No. OF PINS	Α	В	С	D	Insulator Material			
15	0.642	0.984	1.213	0.090	PA9T			
26	0.968	1.311	1.543	0.090	PA9T			
44	1.512	1.852	2.089	0.090	PA9T			
62	2.157	2.500	2.732	0.095	PA6T			

DIMENSIONS (mm)									
No. OF PINS	Α	В	С	D	Insulator Material				
15	16.30	25.00	30.80	2.29	PA9T				
26	24.60	33.30	39.20	2.29	PA9T				
44	38.40	47.05	53.05	2.29	PA9T				
62	54.80	63.50	69.40	2.41	PA6T				

COMPLIANT

MATERIALS AND FINISH:

SHELL: STEEL MATERIAL, NICKEL FINISH INSULATOR: PA9T or PA6T, UL 94V-0 RATED, BLACK

(PROCESS TEMP 260°C)


(PROCESS TEMP 200

CONTACT MATERIAL: BRASS

CONTACT FINISH: SEE P/N KEY BELOW

ELECTRICAL:

CONTACT CURRENT RATING: 3 AMPS
CONTACT RESISTANCE: 10 mOHMS Max.
DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
INSULATION RESISTANCE: 5 GOHMS Min.
TEMPERATURE RATING: -55° ~ +125° C



LIN

UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

1 = GOLD FLASH, ENTIRE CONTACT 2 = 30u" GOLD, ENTIRE CONTACT 3 = 50u" GOLD, ENTIRE CONTACT



RoHS

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

03/19/2007



 SCALE:
 SHEET
 OF
 REV

 NTS
 1
 4
 24

 DWG NO.
 181-MYY-2YYRYYY


DESCRIPTION: HIGH DENSITY - MACHINED CONTACTS - RIGHT ANGLE

MATERIAL:


COLD ROLLED STEEL

PLATING:

CLEAR ZINC




MOUNTING BRACKET WITH BOARD LOCK HARDWARE OPTIONS 14 & 46



HARDWARE OPTIONS 14

BRACKETS MOUNTED ON CONNECTOR WITH LOCATOR PLATE







THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH

DATE:

TE: 03/19/2007 UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

SCALE: SHEET OF REV

NorComp


 SCALE:
 SHEET
 OF
 REV


 NTS
 2
 4
 24


 DWG NO.
 181-MYY-2YYRYYY


MATERIAL: INSULATION PAPER

0.039" THICK









ROHS COMPLIANT

风

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:
03/19/2007


UNITS = inches [mm]


DO NOT SGALE FROM DRAWING


NorComp

SCALE: SHEET OF REV 24

DWG NO. 181-MYY-2YYRYYY








HOLE PATTERN SHOWN ARE FOR FEMALE





ROHS COMPLIANT

以

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NOTCOMP AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:
03/19/2007

UNITS = inches

DO NOT SGALE FROM DRAWING

NorComp

DWG NO.	181-M			(-) () ()	
NTS	- -	4	4		
SCALE:	SHEET	C)F		
SCALE.	SHEET)F		_

REV

24