



## Main

Range of product	Ovalis C Series
Product or component type	Socket-outlet
Device presentation	Mechanism with fixing frame
Socket number	1
Type of packing	Paint cover
Sale per indivisible quantity	1
Number of terminals per pole	2
Condition of use	Indoor

## Complementary






Device mounting	Flush
Outlet poles configuration	2P + E
Cover type	With shutter
Outlet standard description	Pin earth
Outlet standard deviation	French
Fixing mode	By screws By claws
Colour tint	White (RAL 9003)
Surface finish	Matt
Rated current	16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Service life in cycles	5000 cycles
Electrical durability	5000 cycles
Connections - terminals	Screwless terminals
Shape of screw head	Pozidriv No 1
Height	71 mm
Width	71 mm
Depth	44 mm
Embedding depth	28 mm
Net weight	0.045 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Surface treatment	Antibacterial

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	NF C 61-314
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Bleach Liquid soap Window-cleaning fluid Alcohol Acetone Oil UV resistant Petrol

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	54