



Main

Range of product	Acti 9
Product name	Acti 9 IH
Device short name	IH
Product or component type	Mechanical time switch
Number of channels	1
Function available	Manual time changeover

Complementary

Device application	Building
Load type	230 V AC halogen lamp (1000 W) 230 V AC incandescent lamp (1000 W) 7 fluocompact lamp (11 W) 7 fluocompact lamp (15 W) 7 fluocompact lamp (20 W) 7 fluocompact lamp (7 W) 10 parallel-corrected fluorescent tube conventional ballast (58 W) 15 parallel-corrected fluorescent tube conventional ballast (40 W) 3 parallel-corrected fluorescent tube conventional ballast (100 W)
Cycle duration	24 h
Measurement accuracy	+/- 1 s/day
Maximum number of switchings	48 on - 48 off
Minimum interval duration	15 min
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in VA	2.5 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Battery life	10 year(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Backup time	100 h time and program saving
Mounting support	DIN rail
9 mm pitches	2
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
IP degree of protection	IP20 B
Width	18 mm
Height	90 mm
Depth	66 mm
Net weight	0.101 kg

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	Terminals: IP20 B

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	103 g
Package 1 Height	2 cm
Package 1 width	7 cm
Package 1 Length	11 cm
Unit Type of Package 2	S03
Number of Units in Package 2	110
Package 2 Weight	11.964 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12
Number of Units in Package 3	880
Package 3 Weight	110.192 kg
Package 3 Height	50 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------