

# Impact wrench XGT®

## TW008G

40V max • 1/2" • 760 Nm • 0 – 2  
200 min<sup>-1</sup>

**Extra-compact and efficient brushless impact wrench with  
four power settings**

Powerful and compact, 170 mm-long, 1/2" drive impact wrench. Small size and light weight make this tool easy to use, while offering a max. fastening torque of 760 Nm. Four power settings. 2 LEDs with pre-glow and afterglow functions.



### Technical specifications

|                                         |                                                    |
|-----------------------------------------|----------------------------------------------------|
| Voltage XGT                             | ✓                                                  |
| Nominal Battery Voltage                 | 40 V                                               |
| Brushless Motor                         | ✓                                                  |
| No load speed                           | 0 - 600 / 1200 /<br>1900 / 2300 min <sup>-1</sup>  |
| Max Fastening Torque Impact Drill       | 150 / 200 / 320 /<br>760 Nm                        |
| Nut-busting torque                      | 1100 Nm                                            |
| Tightening Capacity Standard Bolt       | M10 - M24                                          |
| Tightening Capacity High Tensile Bolt   | M10 - M16                                          |
| Impacts per Minute (IPM)                | 0 - 1200 / 1900 /<br>2700 / 2900 min <sup>-1</sup> |
| Drive Square                            | 1/2 "                                              |
| Sound Power Level (L <sub>WA</sub> )    | 108 dB(A)                                          |
| Sound Pressure Level (L <sub>pA</sub> ) | 100 dB(A)                                          |
| Noise Uncertainty (K Factor)            | 3 dB(A)                                            |

### User benefits

- Brushless maintenance-free and long-life motor
- Electronic 4 stage impact power selection for added versatility
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes
- Reverse rotation Auto Stop mode stops after the bolt/nut loosened enough
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Ergonomic soft grip handle provides increased comfort
- Battery protection system automatically shuts off power when the battery level is low

Link to product - [www.makita.uk.com](http://www.makita.uk.com)



# Related products

## Other

User manual

Parts drawing