

SIVACON, base, with cable entry, IPXX, T: 500 mm, W: 800 mm, zinc-plated



| Model                             |                  |
|-----------------------------------|------------------|
| product brand name                | SIVACON          |
| design of the product             | With cable entry |
| design of the surface             | zinc plated      |
| design of the product EMC version | No               |
| material                          | steel            |
| protection class IP               | IPXX             |
| product component                 |                  |
| • ventilation                     | No               |

| Mechanical Design |         |
|-------------------|---------|
| width             | 800 mm  |
| depth             | 500 mm  |
| net weight        | 4 600 g |

| Approvals Certificates   |                   |       |
|--------------------------|-------------------|-------|
| General Product Approval | Test Certificates | other |



[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

|       |             |
|-------|-------------|
| other | Environment |
|-------|-------------|


[Miscellaneous](#)



[Environmental Confirmations](#)

### Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
 Information- and Downloadcenter (Catalogs, Brochures,...)  
<http://www.siemens.com/lowvoltage/catalogs>  
 Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1085-2UB32-0>  
 Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/8MF1085-2UB32-0>  
 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)  
[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1085-2UB32-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1085-2UB32-0)  
 CAx-Online-Generator  
<http://www.siemens.com/cax>  
 Tender specifications  
<http://www.siemens.com/specifications>



last modified:

6/3/2024 

