



Main

Product brand	Schneider Electric
Range	New Unica
Type number	NH3535
Product or component type	Timer

Complementary






Device presentation	Mechanism
Technology type	Electronic
Number of rocker	1
Actuator	Push-button
[Ue] rated operational voltage	230 V AC 50 Hz
Rated current	10 A
Associated fuse rating	16 A
Colour tint	Anthracite (RAL 7021)
Surface finish	Matt
Surface treatment	Painted
Number of modules	2 modules
Number of FUNCTION keys	2
Local signalling	Indicator: 1 LED (red)
Number of outputs	1
Control type	Remote control by auxiliary push-button Local control
Time delay	5 min...8 h
Communication network type	Wireless (2.4 GHz), 2.5 mW at < 50 m
Connected auxiliaries	Unlimited number of push-buttons, distance : 50 m
Marking	Timer symbol
Provided equipment	User manual
Wiring configuration	With neutral
Connections - terminals	Screw terminal
Number of loop terminals	2
Clamping connection capacity	1.5...2.5 mm ² for solid cable(s) 1.5...2.5 mm ² for solid stranded cable(s)
Shape of screw head	Pozidriv No 1 and combi
Tightening torque	0.5 N.m
Material	PC (polycarbonate) GF10 FR: casing Metal: terminals Thermoplastic ABS-UV stabilised: central plate
Device mounting	Flush
Fixing mode	By screws
Type of installation	Indoor installation

Type of packing	Carton
Embedding depth	29 mm
Depth	41 mm
Width	45 mm
Height	45 mm
Net weight	0.045 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for operation	5...40 °C
Ambient air temperature for storage	5...40 °C
IP degree of protection	IP20 IP21 with marking on visual parts
IK degree of protection	IK04
Environmental characteristic	Alcohol Petrol Window-cleaning fluid Bleach Oil Liquid soap Acetone UV resistant
Standards	EN 301-489-17 EN 60669-2-1 EN 60730-2-7 EN 300-328
Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive
Product certifications	FIMKO[RETURN]SEMKO[RETURN]NF[RETURN]VDE[RETURN]EAC[RETURN]NEMKO[RETURN]

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins