

Main

Range of product	Actassi
Product or component type	Equipped angled 19" data panel
Device presentation	Loaded
Provided equipment	Front label holder Rear cable manager 24 RJ45 connectors 2 quick fix 19" mountings
Colour	Dark grey (RAL 7016)
Additional information	Automatic grounding


Complementary

Connections - terminals	IDC
Number of port	24 port of STP
Communication network category	6A
Number of rack unit	1U
Type of connector	S-One
Material	DC01 metal sheet 1.2 mm PA6 plastic part PA66 GF20 plastic part
Width	490 mm
Depth	240 mm
Height	47 mm
Net weight	2.5 kg

Environment

Ambient air temperature for operation	-10...55 °C
Standards	IEC 60297 ISO/IEC 11801:ed. 2.2, 2011 NF C 20-150

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations