



Main

Range of product	TeSys
Device short name	LJ7K
Product or component type	Enclosed DOL starter with integral transformer
Contactor application	Motor control
Poles description	3P
Motor starter type	Non reversing
Motor power kW	0.55 kW at 380/400 V AC 50 Hz
Utilisation category	AC-3
[Uc] control circuit voltage	380...400 V
Thermal protection adjustment range	1...1.6 A
Control type	1 black stop button O 1 white start button I

Complementary

Main function available	Emergency stop Isolation Overload protection Short-circuit protection
Enclosure material	Plastic
Width	175 mm
Height	165 mm
Depth	177 mm
Product weight	2.27 kg

Environment

Standards	IEC 60439 IEC 60947 Machinery Directive 98/37/CE
IP degree of protection	IP657 for enclosure