



## Technical data

### NU2218C3

Single row cylindrical roller bearings

Single row cylindrical roller bearing, floating, separable, pressed steel cage

#### VISUAL (S)



## PRODUCT DEFINITION

|                                     |        |
|-------------------------------------|--------|
| <b>Brand</b>                        | NTN    |
| <b>d - Internal diameter</b>        | 90 mm  |
| <b>D - External diameter</b>        | 160 mm |
| <b>B - Bearing/Inner ring width</b> | 40 mm  |
| <b>E - Upper roller diameter</b>    | 143 mm |
| <b>F - Under roller diameter</b>    | 107 mm |
| <b>rs - Min fillet radius</b>       | 2 mm   |
| <b>r1s - Min fillet radius</b>      | 2 mm   |
| <b>Radial clearance class</b>       | C3     |
| <b>Mass</b>                         | 3,1 kg |

## PRODUCT PERFORMANCE

|                                               |              |
|-----------------------------------------------|--------------|
| <b>C - Dynamic load</b>                       | 219000000 mN |
| <b>C0 - Static load</b>                       | 248000000 mN |
| <b>Cu - Fatigue limit load</b>                | 28300000 mN  |
| <b>N lim - Oil lubrication limit speed</b>    | 27600 °/s    |
| <b>N lim - Grease lubrication limit speed</b> | 23400 °/s    |
| <b>Tmin - Min operating temperature</b>       | 233,15 °K    |
| <b>Tmax - Max operating temperature</b>       | 393,15 °K    |

## ABUTMENT

|                                                  |        |
|--------------------------------------------------|--------|
| <b>da min - Min shoulder diameter IR</b>         | 99 mm  |
| <b>da max - Small face shoulder max diameter</b> | 105 mm |
| <b>db min - Min inner ring GO diameter</b>       | 109 mm |
| <b>Da max - Max shoulder diameter OR</b>         | 151 mm |



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

## ABUTMENT

|                                   |      |
|-----------------------------------|------|
| <b>ra max - Max fillet radius</b> | 2 mm |
| <b>r1a - Max fillet radius</b>    | 2 mm |

## INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = Fr$$

Equivalent static radial load

$$P_0 = Fr$$



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15