



Main

Range of product	Odace
Product or component type	Intallation kit
Device presentation	Complete product
Device application	Light control
Condition of use	Indoor

Complementary

Device mounting	Ceiling
Technology type	Electromechanical
Fixing mode	By screws
Colour tint	White (RAL 9003)
Surface finish	Matt
Type of packing	Gift box
Rated current	6 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Load type	LED lamp: 100 W 230 V halogen lamp: 1380 W 230 V AC fluocompact lamp: 1380 W 230 V AC compact fluorescent lamp: 1380 W 230 V AC incandescent lamp: 1380 W
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un with $\cos \varphi = 0.3$
Service life in cycles	150000 cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$
Electrical durability	20000 cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$
Clamping connection capacity	1 x 0.75...2 x 1.5 mm ² for rigid cable(s)
Wire stripping length	10 mm
Light source	Bulb not included
Local signalling	Multi-colour LED
Material	PC (polycarbonate) FR: body and cover Brass alloy: contact
Height	80 mm
Width	80 mm
Depth	39.9 mm
Embedding depth	34.7 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Net weight	0.059 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-20...60 °C
Dielectric strength	2000 V
Standards	EN 60669-1 EN 60669-2-1 EN 301-489-1 EN 301-489-17 EN 61000-6-2 EN 61000-6-3
Product certifications	CE: WD21101201[RETURN]LCIE
IK degree of protection	IK04
IP degree of protection	IP20
Environmental characteristic	Indoor use

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information