



Part Number : [1053001200](#)
Product Description : Nano-Fit Crimp
Terminal, Female, 0.38µm Gold (Au) Plating,
24-26 AWG
Series Number : 105300
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings


[Drawing 1053001200_sd.pdf](#)
[Packaging Design Drawing PK-105300-100-000.pdf](#)

Specifications

[Application Specification AS-105300-100-001.pdf](#)
[Product Specification 1053001000-PS-CH-000.pdf](#)
[Product Specification 1053001000-PS-ES-000.pdf](#)
[Product Specification 1053001000-PS-JP-000.pdf](#)
[Product Specification 1053001000-PS-SK-000.pdf](#)
[Product Specification PS-105300-100-001.pdf](#)
[Test Summary 1053000000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	105300
Description	Nano-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 24-26 AWG
Application	Power, Wire-to-Board
Product Family	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	889056003254

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	50
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.100/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	1.250µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.30mm
Wire Size (AWG)	24, 26
Wire Size mm ²	0.13-0.20

Use with Part(s)

Description	Part Number
Nano-Fit TPA Capable Single Row Receptacle Housings	<u>105307</u>
Nano-Fit TPA Capable Dual Row Receptacle Housings	<u>105308</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG	<u>0638244600</u>
Hand Crimp Tool for Nano-Fit Receptacle Terminals, 24 AWG and 26 AWG, UL1061 and UL1007 Insulations	<u>0638276000</u>
FineAdjust Applicator for Insulation OD 0.90-1.15mm - UL1061	<u>0639032500</u>
FineAdjust Applicator for Insulation OD 1.20-1.45mm - UL1007	<u>0639034800</u>

Application Tooling

Japan

Description	Part Number
S-1 Applicator for Nano-Fit Terminals, 24-26 AWG, UL1061 Wires	<u>2047483710</u>
S-1 Applicator for Nano-Fit Terminals, 24-26 AWG, UL1007 Wires	<u>2047483720</u>