




XFP

TE Internal #: 1542706-3

XFP Heat Sink, Pin Fin, 72 Fin, 10 W / 15 W / 5 W, XFP

[View on TE.com >](#)

Connectors > Connector Accessories > Heat Sinks



Device Type: XFP

Fin Style: Pin Fin

Number of Fins: 72

Power Rating: 5 W, 10 W, 15 W

Features

Product Type Features

| | |
|-------------|-----|
| Device Type | XFP |
|-------------|-----|

Configuration Features

| | |
|----------------|----|
| Number of Fins | 72 |
|----------------|----|

Electrical Characteristics

| | |
|--------------|-----------------|
| Power Rating | 5 W, 10 W, 15 W |
|--------------|-----------------|

Body Features

| | |
|----------------------------------|--------------------|
| Primary Product Material | Aluminum |
| Primary Product Plating Material | Electroless Nickel |
| Fin Style | Pin Fin |

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



| | |
|---|---|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | XFP



Customers Also Bought



Documents

Product Drawings

[XFP. MSA NETWORK APPLICATION H](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1542706-3_K.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1542706-3_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1542706-3_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

