

Endress+Hauser Vibronic level switch FTM21-4A345A

Single rod probe with extension tube for point level detection in bulk solids, also for dust and hazardous areas.



Picture for reference only. Product appearance may vary based on configuration

Soliphant FTM21 is a point level switch for applications with fine-grained or coarse-grained, non-fluidized bulk solids. The various designs means the device has a wide range of applications. Certificates are also available for use in dust and hazardous areas.

- Easy commissioning (plug and play)
- No calibration required
- Measurement not affected by build-up or external vibration
- No mechanically moved parts, free of maintenance
- Not affected by flow noises

Configuration of FTM21-4A345A:

| | | |
|-----------------------|---|------------------------------------|
| Approval: | 4 | ATEX II 1/2D Ex t IIIC Da/Db |
| Process Connection: | A | Thread EN10226 R1, 316L |
| Sensor Length: | 3 | 1000mm |
| Electronics; Output: | 4 | FEM24; relay DPDT, 19-253VAC/55VDC |
| Housing; Cable Entry: | 5 | F18 Alu IP66/67 NEMA4X; M20 gland |
| Additional Option: | A | Basic version |

Alternative part number: FTM21-4A345A