

**RT50S****Article number: 115-06319**

The RELK and RLT cable ties can be re-opened and re-used.

The extended pawl allows for the quick and simple release of the ties. Manufactured in various grades of PA66 these products are suitable for indoor, outdoor and high temperature applications.

Used in a wide range of industries these releasable and reusable ties are ideal where temporary installation or the addition or removal of cables is required, for example: theatres, outdoor events and harness work.

**Base Data**

Colour	Natural (NA)
EDP Text 1 Germany	Wiederöffnungsbinder 165x4,6
EDP Text 2 Germany	RT50S Natur 100 ST ME
Fixation Method (FF)	None
Identification Plate Position	none
Releasable Closure (Yes/No)	Yes
Short Description	6.5", 50 lb., releasable cable tie, natural, 100/bag
Tie Closure	plastic pawl
Type	RT50S.NN3P
Variant	Inside Serrated

Product Dimensions

Bundle \varnothing max.	35 mm
Bundle \varnothing max. (imperial)	1.38 "
Bundle \varnothing min.	1.5 mm
Bundle \varnothing min. (imperial)	0.06 "
Height (H)	1.4 mm
Height (H) (imperial)	0.055 "
Length (L)	165 mm
Length (L) (imperial)	6.5 "
Min. Tensile Strength (N)	225 N
Min. Tensile Strength (lbs)	50 lbs
Thickness (T)	1.2 mm
Width (W)	4.6 mm
Width (W) (imperial)	0.18 "

Logisitic and Packaging

Carton Quantity	5000
EAN code	4031026108414
Pack Cont.	100
Quantity of Europallet	0
Quantity per	Bag
UPC	89306045601

Weight (Kg) 1.2 kg

Material and Specifications

CSA Certified	FALSE
Flammability	UL94 V2
Material	Polyamide 6.6 (PA66)
Material	PA66
Operating Temperature	-40 °C to +85 °C, intermittent +105 °C (for 500 h)
Specification	UL

More Information

UNSPSC Key 39121703

© HellermannTyton 2012