



50W 0-10V 'Dim to Dark' LED Drivers

Input characteristics

Input voltage AC	120-250V (ENEC approved) 120-277V (UL approved)
Input voltage DC	120-250V
Input current	0.65A max
Input frequency	50-60Hz
Efficiency @ full load	86%
Efficiency @ 2/3 load	≥85%
Power factor @ full load	>0.9C
THD @ full load	<20%
Inrush current	negligible: 30mA ² s @ 277V
Surge protection	2kV DM, 2kV CM
Standby power	<0.5W

Output characteristics

LED output power	50W max
LED output current range	150-1,400mA (settable)
LED output current resolution	programmable in 1mA steps
LED output current tolerance	+/- 5%
LED outputs	2 (UL Class 2)
LED output voltage range	1.5 - 55V

Control characteristics

Control channels	1
Dimming protocol	0-10V
Dimming range	100%-0%
Dimming curve	linear, logarithmic, square, or soft-linear
Dimming method	Hybrid HydraDrive
Driver configuration	with TOOLbox pro and FluxTool
0-10V isolation	to line voltage input: 1500V to LED output: 3750V
0-10V current draw	<2mA

Product offering




SOLOdrive 561/U

P/N: SL0561U1

SOLOdrive AC, 50W, 0-10V, 1 control channel, constant current, 2x 55V outputs, long metal

Order number configuration



P/N: for LED driver part number, see 'Product offering' above.

LED output current: in 1mA steps, e.g. "0258", "1011", etc.

Dimming curve: enter "LOG" for a logarithmic, "LIN" for a linear, "SQU" for a square, or "SLN" for a soft-linear dimming curve.

Minimum dimming level: write to one decimal place, e.g. "05.0" for 5%, "07.5" for 7.5%, "10.1" for 10.1%, etc. Leave blank if default minimum dimming level (0.1%) is required.


Protection

LED output short	yes
Overload	yes
Reverse polarity	yes, for LED output
Restart after protection	yes

Dimensions, weight and packaging

SOLOdrive 561/U

LxWxH	444x29.9x21mm
Weight	372 g
Items per carton	28 pcs



Standards and certifications

Standards compliance

UL, Recognized Component	UL 1310, UL 8750 (Class 2 output) Type TL LED driver
EN	61347-1/-2-13, 62384, 55015, 55022, 61000-3-2, 61547
FCC	FCC 47 CFR Part 15 Class B
RoHS2	

Certifications



Wiring Specifications

Wire type	AWG 20-16, 0.5-1.5mm ² solid or stranded copper
Wire strip length	9mm

Wiring diagrams

SOLOdrive 561/U

120-277 VAC —
0-10V —



— LED output
— LED output
— LEDcode / NTC

Thermal protection

External NTC thermistor	throttling @ 70 °C (settable)
External thermistor value	47kΩ
Recommended thermistors	238164063473 (leaded) NTCASCWE3473J (screw)

Thermal specification

Ta operating range	-20 °C ... +50 °C
Tc max	80 °C
Tc lifetime	80 °C
Lifetime @ Tc lifetime	50,000 hours
Type TL	@1400mA: Tref 67 °C, max 86 °C

Warranty

Warranty period	3 years
-----------------	---------