

Product datasheet

Specifications



Electronic thermal overload relay, TeSys Giga, 160-630 A, class 5E-30E, push-in control connection

LR9G630

EAN Code: 3606481912589

Main

Range	TeSys
product name	TeSys LRG
Product or component type	Electronic thermal overload relay
Device short name	LR9G
Relay application	Motor protection
Network type	AC
Thermal overload class	Class 5E...30E conforming to IEC 60947-4-1
Thermal protection adjustment range	160...630 A

Complementary

Network frequency	30...60 Hz 100 Hz
Overvoltage category	III
Tripping threshold	1.125 +/- 0.07 In conforming to IEC 60947-4-1
Protection type	Ground fault protection - tripping time adjustment: 0...1 s - for alarm circuit conforming to IEC 60947-4-1 Ground fault protection - tripping time adjustment: 0...1 s - for alarm circuit conforming to UL 60947-4-1 Phase loss - tripping time adjustment: 0...4 s - for alarm circuit Phase imbalance - tripping time adjustment: 0...5 s - for alarm circuit conforming to IEC 60947-4-1 Phase imbalance - tripping time adjustment: 0...5 s - for alarm circuit conforming to UL 60947-4-1
Local signalling	LED Trip indicator
Contacts type and composition	1 NO + 1 NC
[Ith] conventional free air thermal current	5 A
[Uc] control circuit voltage	24...500 V AC 50/60 Hz 24...250 V DC
[Ue] rated operational voltage	1000 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
Reset	Automatic reset Manual
Mechanical durability	7000 cycles
Surge withstand	4 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electromagnetic compatibility	EMC immunity conforming to IEC 60947-4-1 Emission tests criteria A conforming to IEC 60947-4-1 Immunity to radiated radio-electrical interference - test level: 20 V/m conforming to EN/IEC 61000-4-3 Voltage dips and interruptions immunity test conforming to SEMI F47
Connections - terminals	Power circuit: bar - busbar cross section: 50 x 10 mm Power circuit: lugs-ring terminals 1 300 mm² Control circuit: push-in 1 0.2...2.5 mm² - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.25...2.5 mm² - cable stiffness: flexible with cable end Control circuit: push-in 2 0.5...1.0 mm² with cable end
Tightening torque	58 N.m
Mounting support	Direct on contactor Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ UL 60335-1
Product certifications	CB Scheme CCC cULus UKCA ATEX EU-RO-MR by DNV-GL EAC

Environment

IP degree of protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...60 °C at U _c
Adjustment of dial setting	-25...60 °C
Mechanical robustness	Vibrations 5...300 Hz 6 gn contactor open Shocks 15 gn 11 ms contactor closed
Height	148 mm
Width	211 mm
Depth	186 mm
Net weight	2.9 kg
Colour	Dark grey

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30.000 cm
Package 1 Width	30.000 cm
Package 1 Length	40.000 cm

Package 1 Weight	4.700 kg
------------------	----------

Logistical informations

Country of origin	CN
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	67
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	958748fb-37b2-4e37-985e-0763521c22ab
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

 Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Installation

Installation Videos

[TeSys Giga - How to directly mount LR9G overload relay](#)