

HC-ALU 6-100,5 DKL-COVER GY - End cover



2201123

<https://www.phoenixcontact.com/gb/products/2201123>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile housing, End cover, with hinged flap, with screws and seal, for 100.5 mm profile width (internal), width: 124.4 mm, length: 15 mm, depth: 100.5 mm

Your advantages

- Aluminum extruded profile
- Available in lengths from 100 mm ... 1000 mm, can be cut to any length
- Available in overall widths from 53.5 mm ... 161 mm
- Up to IP65 degree of protection
- Can be used as handheld and wall housing
- Optional EMC seals available

Commercial data

Item number	2201123
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACFAAC
Product key	ACFAAC
Catalog page	Page 769 (C-1-2013)
GTIN	4046356730235
Weight per piece (including packing)	142 g
Weight per piece (excluding packing)	140 g
Customs tariff number	76169910
Country of origin	HU

HC-ALU 6-100,5 DKL-COVER GY - End cover



2201123

<https://www.phoenixcontact.com/gb/products/2201123>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Profile housing
Housing series	HC-ALU
Product family	HC-ALU 6-100,5
Type	End cover, with hinged flap, with screws and seal, for 100.5 mm profile width (internal)
Ventilation openings present	no

Dimensions

Width	124.4 mm
Depth	100.5 mm
Length	15 mm

Material specifications

Color (Housing)	graphite grey (RAL 7024)
Surface characteristics	powder coated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP65
------------------------	------

HC-ALU 6-100,5 DKL-COVER GY - End cover



2201123

<https://www.phoenixcontact.com/gb/products/2201123>

Classifications

ECLASS

ECLASS-11.0	27182701
ECLASS-13.0	27190602

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-ALU 6-100,5 DKL-COVER GY - End cover



2201123

<https://www.phoenixcontact.com/gb/products/2201123>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk