



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cadmium oxide (7.95% in Component part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 4-1393122-7
KHAU-17D11-6=KH


Also in the Series | **Potter & Brumfield KHA**



AC Relays(6)



General Purpose Power Relays(14)




Relay Accessories(5)

Customers Also Bought



TE Part #1776313-8
TSB200008DS=EUROPA T-BL,14.5MM



TE Part #1443403-9
COMP SPLICE CU, LB 4/0 UTILUX



TE Part #2-2176430-5
MPT35 1K0 5%




TE Part #1558661-8
T9GV1L14-48




TE Part #2-1879449-1
TE 400W 47R 5% Bracket




TE Part #CAT-SE594-M1C
M8 Connector: Pigtail Cable, Right Angle



TE Part #7-2176390-7
RQ 1206 7K15 0.1% 10PPM 5K RL



TE Part #3-2176379-7
RQ 0805 255R 0.1% 10PPM 5K RL



TE Part #9-2176378-8
RQ 0805 102R 0.1% 10PPM 5K RL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393122-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393122-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393122-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KHA General Purpose Dry Circuit to 5A Multicontact AC or DC Relay

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English