



21319-281 Boilersuit with kneepad pockets

two-toned - flame retardant - Stretch Zones

MASCOT® ACCELERATE MULTISAFE



S	M	L	XL	2XL	3XL	4XL
5XL						

Main material/upper material

44% modacrylic/30% cotton/20% polyamide/5% aramid/1% carbon fibres

260 g/m²



- A high level of protection with anti-static, acid protection and flame retardant properties.
- Protects from electric arcs.
- The combination of firm fabric and stretch gives you an added freedom of movement.
- CORDURA® reinforcements on the front of the leg - stretch under the CORDURA® material ensures good freedom of movement.
- Easily add holster pockets with the Click Pocket System.
- The inseam length can easily be extended by 3 cm.
- Suitable for Industrial Laundering.

Technical info

Two-toned. Fluorescent with oblique, transverse reflective strips. Anti-static, acid-protective and flame retardant. Protects from electric arcs. Stretch fabric on parts of the product. Prepared for holster pockets with Click Pocket System. Zipper closure and double storm flap with magnet fastening. Chest pocket with a zip. Double stitched seams on the leg and crotch. Ergonomically formed trouser leg. Front pockets. Back pockets with reinforcement and flaps. Reinforced ruler pocket with flap. Thigh pocket with phone pocket and flap with hidden press stud and integrated ID card holder. Adjustable kneepad pockets with CORDURA fabric. Simple individual adjustment of kneepad pocket height. Elastic in the back. Each standard leg length can be lengthened by 3 cm by releasing the internal red stitching. With print effects.

User




Ripstop. According to EN ISO 20471, this product is certified to retain its properties with 50 domestic washes or 40 industrial washes. Impregnation is required after each wash to maintain EN 13034 protection.

Industrial care category B1



Certifications



- OEKO-TEX® STANDARD 100
- EN 1149-5
- EN ISO 11612 (A1, A2, B1, C1, E1, F1)
- EN 13034 (Type 6)
- EN 61482-1-2 APC 1 (torso, front and sleeves APC2)
- EN IEC 61482-1-1 (ELIM 10 cal/cm², ATPV 11 cal/cm², stretch seat area and back ELIM 7,7 cal/cm², ATPV 9,5 cal/cm²)
- EN ISO 20471 - class 3
- Hi-Vis Group Y
- ProWash®

Logo

Due to the unique properties of the fabric, logo printing is only available through the use of specific transfer types. As this is a safety product, we strongly recommend that MASCOT affix the logo to reduce the risk of errors. Please contact customer service for further information.

Logo placement:

- Workwear logo. Special placement. Contact to discuss further