

Eaton 265288

Catalog Number: 265288

Eaton Distribution parts. Impulse relay, 8AC, 1NO+1NC, 16A, 50Hz, 1SU

General specifications



Product Name
Eaton Distribution parts

Catalog Number
265288

EAN
4015082652883

Product Length/Depth
80 mm

Product Height
70 mm

Product Width
17.5 mm

Product Weight
0.136 kg

Compliances
RoHS conform

Product specifications

Mounting method

DIN rail

Control voltage 1 type

AC

Ambient operating temperature - max

45 °C

Ambient operating temperature - min

-20 °C

Control voltage 1 - max

8 V

Control voltage 1 - min

8 V

Control voltage 2 - max

0 V

Control voltage 2 - min

0 V

Frequency control voltage 1 - max

50 Hz

Frequency control voltage 1 - min

50 Hz

Frequency control voltage 2 - max

0 Hz

Frequency control voltage 2 - min

0 Hz

Heat dissipation per pole, current-dependent

1.5 W

Incandescent lamp load - max

0 W

Load fluorescent lamp - max

0 VA

Load fluorescent lamp (duo circuit) - max

0 VA

Load fluorescent lamp (parallel compensated) - max

0 VA

Number of contacts (change-over contacts)

Resources

Declarations of conformity

[DA-DC-03_Z-S](#)

[DA-DC-03_Z-S_SC_SB](#)

Drawings

[eaton-wiring-diagram-z-s-1te.jpg](#)

[eaton-3d-drawing-z-s230-scha2.jpg](#)

[eaton-dimensions-mas-z-s230.jpg](#)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

1

Rated operational current for specified heat dissipation (In)

16 A

Rated switch current

16 A

Equipment heat dissipation, current-dependent

3 W

Supply voltage - max

250 V

Supply voltage - min

250 V

Switching current (cos phi = 0.6) - max

0 A

Width in number of modular spacings

1

Built-in depth

60 mm

Operating mode

Manual operation possible

Control voltage 2 type

AC

Voltage type

AC

Functions

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia