



PRODUCT-DETAILS

CT-ERC.12

CT-ERC.12 Time relay, ON-delay 1c/o, 24-48VDC/24-240VAC



概要信息	
产品型号	CT-ERC.12
产品ID	1SVR508100R0000
欧洲商品编号(EAN)	4013614534317
目录说明	CT-ERC.12 Time relay, ON-delay 1c/o, 24-48VDC/24-240VAC
详细描述	The CT-ERC.12 is a single-function electronic time relay from the CT-C timer range. It provides an ON-delay (delay on make) function with 7 time ranges from 0.05 s to 100 h. This time relay operates with a rated control supply voltage of 24 - 48 V DC / 24 - 240 V AC and has a 1 c/o (SPDT) output rated at 250 V / 4 A.

订货信息	
欧洲商品编号(EAN)	4013614534317
最小起订量	1 piece
海关关税号	85364900

Popular Downloads	
数据手册, 技术资料	2CDC110004C0210_01

说明书和手册	1SVC500020M1001 1SVC500020M0001
CAD Dimensional Drawing	2CDC001079B0201

尺寸

产品净宽	17.5 mm
产品净高	70 mm
产品净深	63 mm
产品净重	0.052 kg

技术参数

计时器继电器类型	ON-Delay
时间量程	0.05 s ... 100 h
额定控制供电电压 (U _s)	24 ... 240 V AC 24 ... 48 V DC
额定工作电压	Auxiliary Circuit 250 V
额定频率 (f)	50 / 60 Hz DC
输出	1 c/o (SPDT) contact
端子类型	Screw Terminals
额定工作电流 AC-12 (I _e)	(230 V) 4 A
额定工作电流 AC-15 (I _e)	(230 V) 3 A
额定工作电流 DC-12 (I _e)	(24 V) 4 A
额定工作电流 DC-13 (I _e)	(24 V) 2 A
最小切换容量	12 V 100 mA
额定冲击耐受电压 (U _{imp})	Input Circuit 4 kV
额定绝缘电压 (U _i)	Input Circuit / Output Circuit 300 V Output Circuit 1 / Output Circuit 2 300 V
防护等级	Housing IP50 Terminals IP20
过电压类别	III
污染等级	3
短路保护设备	Output Circuit NC - F Type Fuses 6 A Output Circuit NO - F Type Fuses 10 A
连接容量	Flexible 1x 0.5 ... 2.5 mm ² Flexible 2x 0.5 ... 1.5 mm ² Rigid 1x 0.5 ... 4 mm ² Rigid 2x 0.5 ... 1.5 mm ²
拧紧力矩	0.5 ... 0.8 N·m
剥线长度	7 mm
推荐的螺丝刀	0.8 x 4 Pozidriv 1
安装位置	1 ... 6
安装到DIN导轨上	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
标准	CAN/CSA C22.2 No.14 IEC/EN 63000 IEC 61812-1 UL 508

UL/CSA适用的技术参数

最高工作电压UL/CSA	Output Circuit 300 V AC
接触等级UL/CSA	B300
连接容量UL/CSA	Flexible 1x 18-14 AWG Flexible 2x 18-16 AWG Rigid 1x 20-12 AWG Rigid 2x 20-16 AWG
拧紧力矩UL/CSA	4.43 ... 7.08 in-lb
接触元件的引导功率符合UL508标准	B300
可燃性符合UL94标准	V-2

环境条件

周围环境温度	Operation -20 ... +60 °C Storage -40 ... +85 °C
允许的最高工作海拔	Without Derating 2000 m

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SVD981001-4501
RoHS信息	1SVD981001-4401
RoHS状态	Following EU Directive 2011/65/EU
SCIP	f001acf5-a161-41e7-b91c-26b273b31434 Germany (DE)
简化的SCIP	d527d098-30d4-49b3-9941-2b6f8d436ba6 Germany (DE) dce31b32-2ca9-4f35-8201-74afad3fdb20 Poland (PL) 29d1fe00-3efe-47ed-975f-587a836e88b6 Norway (NO) 5e268c87-9f91-421c-ab6c-697c8a96143f Hungary (HU) 651f801e-3187-4405-a9bd-3681f014790f Bulgaria (BG) 484ba575-474d-4b9f-be0e-55ab6e742d23 Greece (GR) 85797548-20ab-4979-8ce8-81ae70f4157d Estonia (EE) 46968d40-0530-4dc3-b297-af073e0053e3 Sweden (SE) 7aabb9c-9fcc-4fa6-9201-e4947ae1b035 Sweden (SE) b6a9253a-41ac-43d3-bd43-d52e49620036 France (FR) 47456910-883f-4229-872e-ff2e3bf990e5 Poland (PL) 8befcbde-59bc-4239-8607-9baf3a2104fd Denmark (DK) 09a69f1c-7421-4fc4-a87e-1dda0a19de2d Germany (DE) 2c142811-af17-41c8-9cd0-69f335a40a63 Belgium (BE) 8f3175e1-3632-4adf-88b4-88de7a637d88 Italy (IT) eb5be464-17fe-469f-9ef4-b57aa5491747 Finland (FI) 63d29f79-95e6-4f3b-8e1c-3cf5b3d92f20 Poland (PL) 54834da2-6d3c-41cf-af14-a78fd76912f0 Netherlands (NL) eb003df3-740d-4b68-ab79-0479e79a5180 Croatia (HR) 678402d9-6488-42a9-bb82-023822848993 Czech Republic (CZ) c8d28db5-e6e7-4778-babd-b859d1106adc Belgium (BE) e5e5e0b5-0715-47bd-9a82-8fd5575f0bc4 Germany (DE) aa420a6b-fb07-479f-a31f-dc1b5fbae610 Germany (DE) bb53bdd9-b874-4fa8-b88a-a81010f968f9 Hungary (HU) 1568b01e-f642-4863-8406-a744e191f387 France (FR) 3a3ed994-5394-42a0-b748-2becbd9ebebc Spain (ES) 271a1a89-17ee-49b1-8013-ce4d89b68b25 Portugal (PT)
Toxic Substances Control Act - TSCA	2CMT2023-006536

ABB EcoSolutions

产品寿命终止后的拆解指南	1SAC200318H0001
--------------	-----------------

认证及声明（文件编码）	
CCC认证	CCC_2019010303150608
CQC认证	CQC2019010303150608
cULus 认证	cULus_20031209-E140448
Declaration of Conformity - CCC	2020980303000209
符合性声明 - CE	1SVD981068
Declaration of Conformity - UKCA	1SVD981068-10
DNV GL Certificate	DNV_GL_TAA00002TS

包装信息	
1级包装单元	box 1 piece
1级包装宽度	89 mm
1级包装长度	20 mm
1级包装高度	65 mm
1级包装 总重	0.065 kg
1级包装 EAN	4013614534317

分类	
对象分类代码	K
ETIM 7	EC001439 - Timer relay
ETIM 8	EC001439 - Timer relay
ETIM 9	EC001439 - Timer relay
e级	V11.0 : 27371605
UNSPSC	39122329
E-Number (Finland)	2712827
E-Number (Norway)	4189318
E-Number (Sweden)	4030218

分类	
低压产品及系统 → 控制产品 → 电子继电器与控制器件 → 时间继电器 → CT-C	

