



ANDROS+ - S2

Réf. : 15210



Suitable for :	Inside
Type :	Ankle shoe
Activity :	Food industry, Catering, Medical / Chemical Industry
Upper :	Dry-Tek® material thickness 2.2 mm acids resistant, washable and breathable
Lining :	Cambrelle Amicor+® lining with ???Refreshing??? microcells perfume system
Tongue :	Dry-Tek® material
Ankle protection :	Synthetic PU material with 10 mm foam
Fastening :	Pull on style with elastic strap
Toe cap :	Composite 200 joules Light System®
Midsole :	
Insole :	Antibacterial and antimicrobial foam
Sole :	PU 2D, oil resistant FO, antistatic and HI-CI
Sole pattern :	Special non-slip crampons for smooth and greasy floors, SRC standard
Weight (Kg/pair) :	0.800
Colors :	White upper and white/light grey outsole
Sizes :	35-48 (2-13)
Standard :	EN ISO 20345:2011 SRC
CE certificate of conformity N° :	0075/020/161/04/13/0269 - EXT 02/04/13
Special features :	Upper without side stitching: no water infiltration risks
Special features 2 :	Dry-Tek® material resistant to 12 acids and corrosive fluids (standard EN 13832-2)
Special features 3 :	Boot loop on the back to put the shoe on easier

SPECIAL FEATURES

-  200 joules light composite toecap
-  Metal free, non magnetic
-  Water absorption and penetration resistance of upper (WRU)

Cambrelle+
with
Amicor+
PLUS

GENERAL FEATURES

	Antistatic properties (A)	200	200
	Heel energy absorption (E)	200	200
	Abrasion resistance	200	200
	Crampon sole	200	200
	Heat-insulated sole (HI)	200	200
	Cold-insulated sole (CI)	200	200
	200 joule extra-wide toecap	200	200
	Hyper-ventilated lining	200	200
	Perforation-resistance 1100 N (P)	200	200