

### AEACAC053010-S868



53.4 x Ø10.4 mm RoHS/RoHS II Compliant MSL = 1

#### **Features**

- 868 MHz LPWA/ISM antenna
- Linear polarization
- Gain of 2 dBi
- Compact, low profile whip antenna

## **Applications**

- LPWA/LoRa/SigFox applications
- ISM applications
- IoT
- M2M
- Remote technology/monitoring
- Network devices
- Smart buildings
- Smart city
- Agriculture/environment
- Consumer tracking

### **Electrical Characteristics**

Parameters	Min.	Тур.	Max.	Units	Note
Frequency Range		868		MHz	
VSWR			3		
Polarization	Linear				
Impedance		50		Ω	
Gain		2	·	dBi	Zenith

### **Mechanical Characteristics**

Parameters	Description
Mounting	Connector
Connector	SMA Male

### **Environmental Characteristics**

Parameters	Description
Operating temperature	-40°C to +85°C
Vibration	10 to 55 Hz with 1.5 mm amplitude 2 hours






### AEACAC053010-S868



53.4 x Ø10.4 mm RoHS/RoHS II Compliant MSL = 1

# Dimensions (Unit: mm)



### **Product**








AEACAC053010-S868



53.4 x Ø10.4 mm RoHS/RoHS II Compliant MSL = 1

#### **VSWR**



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.





### AEACAC053010-S868



53.4 x Ø10.4 mm RoHS/RoHS II Compliant MSL = 1


### **Radiation Pattern**


## <u> 2D – Pattern</u>

# Frequency: 868 MHz

### **Horizontal Plane**








### 3D - Pattern

Frequency: 868 MHz



Frequency (MHz)	Efficiency	Gain (dBi)
868	0.61	2.11

### **Package**

A carton weighs about 8 Kg with 1,000 pieces each of dimension 37 x 36 x 17 cm.

