

# P813 P813C

Rotary Burr – Pointed Tree. Brazed above 6.00 mm.

| P813<br>P813C | P1.1 | P1.2 | P1.3 | P2.1 | P2.2 | P2.3 | P3.1 | P3.2 | P3.3 | P4.1 | P4.2 | P4.3 | M1.1 | M1.2 | M2.1 | M2.2 | M2.3 |
|---------------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
|               | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    |
|               | M3.1 | M3.2 | M3.3 | M4.1 | M4.2 | K1.1 | K1.2 | K1.3 | K2.1 | K2.2 | K2.3 | K3.1 | K3.2 | K3.3 | K4.1 | K4.2 | K4.3 |
|               | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    |
|               | K4.4 | K4.5 | K5.1 | K5.2 | K5.3 | N3.1 | N3.2 | N3.3 | S1.1 | S1.2 | S1.3 | S2.1 | S2.2 | S3.1 | S3.2 | S4.1 | S4.2 |
|               | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    | ■    |
|               | H1.1 | H2.1 | H2.2 | H3.1 | H3.2 | H4.1 | H4.2 |      |      |      |      |      |      |      |      |      |      |
|               | ■    | ■    | ■    | ■    | ■    | ■    | ■    |      |      |      |      |      |      |      |      |      |      |

|       |    |   |                                                                                   |                                                                                   |                                                                                   |                                                                                   |    |                                                                                     |                                                                                        |                                                                                        |
|-------|----|---|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|
| P813  | HM | G |  |  |  |  | DC |  |  40 |  40 |
| P813C | HM | G |  |  |  |  | DC |  |  40 |                                                                                        |





| P813                                                                                 | P813C                                                                                |
|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|  |  |
| 3.00 – 16.00                                                                         | 3.00 – 12.70                                                                         |

| DC    | DCON MS h7 | APMX | OAL  | P813                      | P813C                      |
|-------|------------|------|------|---------------------------|----------------------------|
| [mm]  | [mm]       | [mm] | [mm] |                           |                            |
| 3.00  | 3          | 14   | 38   | P8133.0X3.0 <sup>1)</sup> | P813C3.0X3.0 <sup>1)</sup> |
| 6.30  | 3          | 12.7 | 45   | P8136.3X3.0               |                            |
| 6.00  | 6          | 18   | 50   | P8136.0X6.0 <sup>1)</sup> | P813C6.0X6.0 <sup>1)</sup> |
| 8.00  | 6          | 19   | 64   | P8138.0X6.0               |                            |
| 9.60  | 6          | 19   | 64   | P8139.6X6.0               | P813C9.6X6.0               |
| 12.70 | 6          | 25   | 70   | P81312.7X6.0              | P813C12.7X6.0              |
| 16.00 | 6          | 25   | 70   | P81316.0X6.0              |                            |

<sup>1)</sup> DCON MS tolerance h6