

Front plate - VS-SI-FP-2RJ-MOD - 1656631

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Front plate, plastic with shroud, for 2x RJ with modular system (Keystone)



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356030007
Weight per Piece (excluding packing)	28.100 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	40 mm
Width	51 mm
Length	87.5 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

General

Color	gray
Torque	0.9 Nm ±0.1 Nm (M4, thread tightening torque shroud)
Housing material	PBT
Flammability rating according to UL 94	V0
Assembly instructions	suitable for all mounting frames

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Front plate - VS-SI-FP-2RJ-MOD - 1656631


Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Front plate

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27189239
eCl@ss 5.1	27189200
eCl@ss 6.0	27189200
eCl@ss 7.0	27189217
eCl@ss 8.0	27189217
eCl@ss 9.0	27189217

ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007
ETIM 4.0	EC000007
ETIM 5.0	EC000456
ETIM 6.0	EC000456

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121302

Front plate - VS-SI-FP-2RJ-MOD - 1656631

Accessories

Accessories

Device marking

Snap-in markers - UCT-EM (20X7) - 0801494



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 20 x 7 mm

Marking material

Marker labels - VS-SI-BZ - 1656660



Marker label, plastic, plate with 20 labels