



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(5)



Connector Contacts(51)



Connector Hardware(46)



Power Contacts(51)



Rectangular Connector Housings(77)



Rectangular Power Connectors(82)



Standard Rectangular Connectors(81)

Customers Also Bought



TE Part #YDIV40E21-11PNC009
RECP ASSY



TE Part #2000713-8
RA Keyed Guide Mod, Vita 46,
Machined



TE Part #2-327950-1
PIDG RECT 22-16COMM 22-18MIL 5



TE Part #3-1618400-8
DS11-1005T=SOLID STATE RELAY



TE Part #YDTS20T17-06PNV001
RECP ASSY



TE Part #1053372-1
2062 8001 90,OSM JACK, QPL



TE Part #1757829-3
AMPLIMITE,PLUG ASY,POSTD,109,ZN,
3



TE Part #YCTJ720K01BC017000
MODULE ASSY



TE Part #53410-1
TERMINAL,PIDG PVF2 R 22-16 1/4



TE Part #YDTS24T21-11PAV001
RECP ASSY

Documents



CAD Files

Customer View Model

ENG_CVM_CVM_200871-1_Y.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_200871-1_Y.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_200871-1_Y.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP Jack Screw Selection Chart for Series "M", COAXICON and Miniature

English

Instruction Sheet (U.S.)

English

AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS

English

Instruction Sheet (U.S.)

English

75 and 104 Position Series "M" Connectors and Accessories

English

Instruction Sheet (U.S.)

English

21 & 26 POSITION SERIES "M" CONNECTORS AND ACCESSORIES

English