

BDS2A25010RK

✓ ACTIVE


CGS | CGS BDS

TE Internal #: 1614770-4
10 ohm Chassis Mount Resistor, 250 W, Thick Film, 2 Terminations,
±150 ppm/°C, 10 %, Screw Terminals, Loose Piece - Tray, CGS BDS

[View on TE.com >](#)



Passive Components > Resistors > Chassis Mount Resistors > Resistor Power BDS2A – High Power



Resistor Type: **Power Resistor**
Resistance Class: **Up to 1kΩ**
Resistance Value: **10 Ω**
Power Rating: **250 W**
Element Type: **Thick Film**

[All Resistor Power BDS2A – High Power \(108\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Class	Up to 1kΩ
Resistance Value	10 Ω
Power Rating	250 W
Passive Component Tolerance	10 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Screw Terminals

Mechanical Attachment



Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Dimensions

Product Height	36 mm[1.417 in]
Product Length	67 mm[2.638 in]
Product Width	60.25 mm[2.372 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C
Temperature Coefficient	±150 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (33.3% in component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # CAT-C339-B349
Resistor Power BDS2A100



TE Part # 2-1614770-2
BDS 2 A 250 3R3 10%

Also in the Series | CGS BDS




Chassis Mount Resistors(150)

Customers Also Bought



TE Part #ZPF000000000040015
983-7WS 14-04 PN



TE Part #ZPF000000000002015
182-0664-06



TE Part #1-2176080-3
EP 9W 1K0 5%




TE Part #1-87499-2
06 MODIV HSG COMP SR .100CL



TE Part #5-1623932-7
CFR50 5% 220K



TE Part #1-1623932-1
CFR50 5% 10R



TE Part #GA100K6A1B
DISCRETE 100K OHM, +/-0.2C FROM 0C TO 70C



TE Part #3-1625958-4
HB01RE 500M 1% 100PPM

BDS2A25010RK

10 ohm Chassis Mount Resistor, 250 W, Thick Film, 2 Terminations, ±150 ppm/°C, 10 %, Screw Terminals, Loose Piece - Tray, CGS BDS



Documents

Product Drawings

BDS 2 A 250 10R 10%

English

CAD Files

Customer View Model

ENG_CVM_CVM_1614770-4_S.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1614770-4_S.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1614770-4_S.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Thick Film Power Resistors - Type BDS250/400 Series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English