

SIEMENS

Product data sheet

6GK5112-2BB00-2AA3

Product-type designation

SCALANCE X112-2


SCALANCE X112-2, UNMANAGED IE SWITCH,
 12 X 10/100MBIT/S RJ45 PORTS,
 2 X 100MBIT/S MULTIMODE BFOC,
 LED-DIAGNOSIS,
 FAULT SIGNAL CONTACT WITH SET BUTTON,
 REDUNDAND POWER SUPPLY,
 INCL. ELECTRON. MANUAL ON CD

Transmission rate

Transfer rate / 1	10 Mbit/s
Transfer rate / 2	100 Mbit/s

Interfaces

Number of electrical/optical connections / for network components or terminal equipment / maximum	14
Number of electrical connections	
• for network components and terminal equipment	12
• for alarm contact	1
• for power supply	1
• for redundant power supply	1
Design of electrical connection	
• for network components and terminal equipment	RJ45 port
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
Number of optical interfaces / for optical waveguide	

• at 100 Mbit/s	2
Design of optical interface / for optical waveguide	
• at 100 Mbit/s	BFOC sockets (multimode up to 5 km)
Connectable optical power relative to 1 mW	
• of the transmitter output	-19 ... -14 dB
• of the receiver input / maximum	-14 dB
Optical sensitivity relative to 1 mW / of the receiver input / minimum	-32 dB
Attenuation / of fiber-optic cable transmission link / minimum necessary	0 dB
Range / at the optical interface / depending on the optical fiber used	0 ... 5 km
Inputs/outputs	
Operating voltage / of signaling contacts / at DC / rated value	24 V
Operating current / of signaling contacts / at DC / maximum	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of supply voltage	DC
Supply voltage / external	24 V
• minimum	18 V
• maximum	32 V
Product component / fusing at power supply input	No
Consumed current / maximum	0.45 A
Active power loss / at 24 V / for DC	5.16 W
Permitted ambient conditions	
Ambient temperature	
• during operating	-10 ... +70 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
Relative humidity	
• at 25 °C / without condensation / during operating / maximum	95 %
Protection class IP	IP30
Design, dimensions and weight	
Design	compact
Width	120 mm

Height	125 mm
Depth	124 mm
Net weight	1.1 kg
Type of mounting	
• 35 mm DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
Standards, specifications, approvals	
Standard	
• for EMC / from FM	FM3611: Class 1, Division 2, Group A, B, C, D / T.., Class 1, Zone 2, Group IIC, T..
• for hazardous zone	EN 60079-0:2006, EN60079-15:2005, II 3 G Ex nA II T.. KEMA 08 ATEX 0003 X
• for safety / of CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for hazardous area / of CSA and UL	UL 1604 and UL 2279-15 (Hazardous Location), Class 1 / Division 2 / Group A, B, C, D / T.., Class 1 / Zone 2 / Group IIC / T..
• for emitted interference	EN 61000-6-4:2001
• for interference immunity	EN 61000-6-2:2001
Verification of suitability	EN 61000-6-2:2001, EN 61000-6-4:2001
• CE mark	Yes
• C-Tick	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	No
letzte Änderung:	Feb 15, 2012