




Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Jumpers & Shunts



Centerline (Pitch): 2.54 mm [.1 in]
Contact Current Rating (Max): 3 A
Circuit Application: Power & Signal
Operating Temperature Range: -40 – 150 °C [-40 – 302 °F]

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board

Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Compatible With Approved Standards Products

UL

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1437212-0
FSK-22A-11




TE Part # 6-1437212-4
FSK-22A-22



TE Part # 4-1437212-9
FSK-22A-10




TE Part # 2386244-1
FSK-22A-27



TE Part # 5-1437212-1
FSK-22A-12




TE Part # 3-1437221-5
FSK-22.5A



TE Part # 7-1437212-2
FSK-22A-4



TE Part # 1474446-1
FSK-22.5A-11V6



TE Part # 6-1437212-2
FSK-22A-20



TE Part # 4-1474671-4
FSK-22A-25V2




TE Part # 6-1437212-9
FSK-22A-3



TE Part # 2205010-1
FSK-22A-17V3


Customers Also Bought



TE Part #8-1532020-7
095-0604-2037=MCDR3-B-9S5L5-0.5




TE Part #1883712-4
A600, SZ2, RCPT 150/150/85



TE Part #4-1617752-5
FCA-215-HZ4



TE Part #1-1617122-2
JMACD-26XM = M39016/15-081M



TE Part #5120521-1
1FHR,64,30A/S,S,N,S08,09,10



TE Part #620001-000
D-100-00



TE Part #2101252-1
A600R,Sz3,150/150//13C2 x2



TE Part #2-320571-2
PIDG R 22-16 COMM 22-18MIL 1/4



TE Part #32996
TERMINAL,SOLIS R 8 8



TE Part #33456
TERMINAL,SOLIS R 12-10 6

Documents



Product Drawings

FSK-22A

English

Product Specifications

Product Specification

English

Agency Approvals

UL Report

English